

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431123

Luminaire Tested: **LAMR4B112R559040DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431123
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-898-142)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B112R559040DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 55 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1298.0 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.81
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431123
CATALOG NUMBER: LAMR4B112R559040DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P431123

CATALOG NUMBER: LAMR4B112R559040DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	95			95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90			90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85			85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80			80
5	96	89	83	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76			76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72			72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	68			68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	72	69	66	65			65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62			62
10	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	63	60	59			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	873578
5°	885830
10°	906543
15°	868639
20°	789245
25°	634262
30°	365124
35°	105945
40°	16166
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P431123

CATALOG NUMBER: LAMR4B112R559040DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.5	13.2
10°-20°	473.1	36.5
20°-30°	510.7	39.3
30°-40°	139.7	10.8
40°-50°	2.9	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1155.4	89.0
0°-40°	1295.1	99.8
0°-60°	1298.0	100.0
0°-90°	1298.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1298.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1771	
5°	1789	172
15°	1701	473
25°	1165	511
35°	176	140
45°	0	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P431123

CATALOG NUMBER: LAMR4B112R559040DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1770.6
2.5°	1763.4
5°	1788.6
7.5°	1808.3
10°	1809.5
12.5°	1763.4
15°	1700.6
17.5°	1617.4
20°	1503.2
22.5°	1355.9
25°	1165.1
27.5°	921.5
30°	640.9
32.5°	351.3
35°	175.9
37.5°	75.4
40°	25.1
42.5°	3.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)