

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P429928

Luminaire Tested: **LAM4B112R459727DE010x1MB**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P429928  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-908-8)  
Test Lab: INNOVATION CENTER (G2)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAM4B112R459727DE010x1MB  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 45 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 97CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1077.6 lumens  
Efficiency: N/A  
Efficacy: 75.4 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.66  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P429928

CATALOG NUMBER: LAM4B112R459727DE010x1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P429928

CATALOG NUMBER: LAM4B112R459727DE010x1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95																			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89																			
3	105	99	94	91	103	98	93	90	95	92	89	93	90	87	90	88	86	85																			
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80																			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76																			
6	92	85	79	76	91	84	79	75	82	78	75	81	77	74	80	77	74	73																			
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69																			
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66																			
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	65	63																			
10	79	71	66	62	78	70	66	62	70	65	62	69	65	62	68	65	62	61																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	995788
5°	995431
10°	946171
15°	831097
20°	635828
25°	371161
30°	151940
35°	64266
40°	35037
45°	22607
50°	17654
55°	15311
60°	12334
65°	9806
70°	9088
75°	8006
80°	8808
85°	5661



TEST NUMBER: P429928

CATALOG NUMBER: LAM4B112R459727DE010x1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	188.1	17.5
10°-20°	443.0	41.1
20°-30°	312.1	29.0
30°-40°	76.8	7.1
40°-50°	26.8	2.5
50°-60°	15.9	1.5
60°-70°	8.8	0.8
70°-80°	4.8	0.4
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	943.2	87.5
0°-40°	1020.0	94.7
0°-60°	1062.7	98.6
0°-90°	1077.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1077.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2018	
5°	2010	188
15°	1627	443
25°	682	312
35°	107	77
45°	32	27
55°	18	16
65°	8	9
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P429928

CATALOG NUMBER: LAM4B112R459727DE010x1MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2018.3
2.5°	2013.0
5°	2009.9
7.5°	1973.3
10°	1888.6
12.5°	1773.6
15°	1627.1
17.5°	1437.9
20°	1211.0
22.5°	950.6
25°	681.8
27.5°	440.3
30°	266.7
32.5°	162.1
35°	106.7
37.5°	75.3
40°	54.4
42.5°	41.8
45°	32.4
47.5°	27.2
50°	23.0
52.5°	19.9
55°	17.8
57.5°	15.7
60°	12.5
62.5°	10.5
65°	8.4
67.5°	7.3
70°	6.3
72.5°	5.2
75°	4.2
77.5°	4.2
80°	3.1
82.5°	2.1
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)