

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431201

Luminaire Tested: **LAMR4B112R709727DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431201
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B112R709727DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1045.7 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431201

CATALOG NUMBER: LAMR4B112R709727DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P431201

CATALOG NUMBER: LAMR4B112R709727DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	64	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50	50	50	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46	46
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	379261
5°	372191
10°	376495
15°	387123
20°	387797
25°	351835
30°	314364
35°	276097
40°	203266
45°	113872
50°	56032
55°	31397
60°	19044
65°	12492
70°	9232
75°	8197
80°	5967
85°	6227



TEST NUMBER: P431201

CATALOG NUMBER: LAMR4B112R709727DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.8	6.9
10°-20°	213.6	20.4
20°-30°	296.4	28.3
30°-40°	278.8	26.7
40°-50°	133.1	12.7
50°-60°	35.2	3.4
60°-70°	11.1	1.1
70°-80°	4.5	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	581.8	55.6
0°-40°	860.6	82.3
0°-60°	1028.9	98.4
0°-90°	1045.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1045.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	769	
5°	752	72
15°	758	214
25°	646	296
35°	458	279
45°	163	133
55°	36	35
65°	11	11
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P431201

CATALOG NUMBER: LAMR4B112R709727DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	768.7
2.5°	759.0
5°	751.5
7.5°	750.4
10°	751.5
12.5°	753.6
15°	757.9
17.5°	757.9
20°	738.6
22.5°	697.8
25°	646.3
27.5°	594.8
30°	551.8
32.5°	509.9
35°	458.4
37.5°	391.9
40°	315.6
42.5°	235.1
45°	163.2
47.5°	108.4
50°	73.0
52.5°	50.5
55°	36.5
57.5°	25.8
60°	19.3
62.5°	14.0
65°	10.7
67.5°	7.5
70°	6.4
72.5°	5.4
75°	4.3
77.5°	3.2
80°	2.1
82.5°	2.1
85°	1.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)