

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P429837

Luminaire Tested: **LAM4B112R259730DE010x1MW**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P429837  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-5)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAM4B112R259730DE010x1MW  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 25 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1152.4 lumens  
Efficiency: N/A  
Efficacy: 80.6 lumens/watt  
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41  
Luminous Opening: Circular (Dia: 0.29' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P429837

CATALOG NUMBER: LAM4B112R259730DE010x1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P429837

CATALOG NUMBER: LAM4B112R259730DE010x1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97																											
2	112	109	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	95																											
3	109	104	101	99	107	103	100	98	101	98	96	99	96	95	96	95	93	92																											
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	94	93	91	90																											
5	103	98	94	91	102	97	93	91	95	92	90	94	91	89	92	90	89	88																											
6	100	95	91	88	99	94	91	88	93	90	87	92	89	87	91	88	86	85																											
7	98	92	88	86	97	92	88	86	91	87	85	90	87	85	89	86	84	83																											
8	96	90	86	83	95	89	86	83	88	85	83	88	85	83	87	84	82	81																											
9	94	88	84	81	93	87	84	81	86	83	81	86	83	81	85	82	81	80																											
10	91	85	82	79	91	85	82	79	84	81	79	84	81	79	83	81	79	78																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	906950
5°	845711
10°	669668
15°	337026
20°	108146
25°	37827
30°	12668
35°	2537
40°	841
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P429837

CATALOG NUMBER: LAM4B112R259730DE010x1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	463.0	40.2
10°-20°	561.6	48.7
20°-30°	114.3	9.9
30°-40°	12.9	1.1
40°-50°	0.6	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1138.8	98.8
0°-40°	1151.8	99.9
0°-60°	1152.4	100.0
0°-90°	1152.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1152.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5630	
5°	5230	463
15°	2021	562
25°	213	114
35°	13	13
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P429837

CATALOG NUMBER: LAM4B112R259730DE010x1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5629.6
2.5°	5520.8
5°	5229.5
7.5°	4748.8
10°	4093.6
12.5°	3155.1
15°	2020.7
17.5°	1138.4
20°	630.8
22.5°	359.4
25°	212.8
27.5°	127.3
30°	68.1
32.5°	29.8
35°	12.9
37.5°	8.0
40°	4.0
42.5°	1.5
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)