

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430964

Luminaire Tested: **LAMR4B112R209730DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430964
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-3)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B112R209730DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 20 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1137.5 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.33
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430964

CATALOG NUMBER: LAMR4B112R209730DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P430964

CATALOG NUMBER: LAMR4B112R209730DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97
2	112	108	105	103	110	106	104	102	103	101	100	101	99	97	98	97	95	94	94	94	94
3	108	104	100	98	107	103	100	97	100	98	96	98	96	94	96	94	93	91	91	91	91
4	105	100	97	94	104	99	96	93	97	94	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83	83	83	83
8	96	90	86	83	95	89	86	83	88	85	83	87	85	82	87	84	82	81	81	81	81
9	94	88	84	81	93	87	84	81	86	83	81	86	83	81	85	82	81	80	80	80	80
10	92	86	82	80	91	85	82	80	85	82	79	84	81	79	83	81	79	78	78	78	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3929472
5°	3321440
10°	1950908
15°	698548
20°	231124
25°	92001
30°	43981
35°	25116
40°	18163
45°	15281
50°	17577
55°	14365
60°	7203
65°	6071
70°	7501
75°	8006
80°	5967
85°	5661



TEST NUMBER: P430964

CATALOG NUMBER: LAMR4B112R209730DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	549.1	48.3
10°-20°	428.2	37.6
20°-30°	88.9	7.8
30°-40°	28.0	2.5
40°-50°	18.0	1.6
50°-60°	14.5	1.3
60°-70°	5.7	0.5
70°-80°	4.3	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1066.3	93.7
0°-40°	1094.3	96.2
0°-60°	1126.8	99.1
0°-90°	1137.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1137.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7964	
5°	6706	549
15°	1368	428
25°	169	89
35°	42	28
45°	22	18
55°	17	14
65°	5	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P430964

CATALOG NUMBER: LAMR4B112R209730DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	7964.4
2.5°	7672.3
5°	6706.4
7.5°	5373.2
10°	3894.1
12.5°	2456.6
15°	1367.6
17.5°	752.1
20°	440.2
22.5°	269.1
25°	169.0
27.5°	111.6
30°	77.2
32.5°	54.2
35°	41.7
37.5°	33.4
40°	28.2
42.5°	24.0
45°	21.9
47.5°	21.9
50°	22.9
52.5°	21.9
55°	16.7
57.5°	11.5
60°	7.3
62.5°	6.3
65°	5.2
67.5°	5.2
70°	5.2
72.5°	5.2
75°	4.2
77.5°	3.1
80°	2.1
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)