

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431858

Luminaire Tested: **LAMR4B412R309027DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431858
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B412R309027DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5322.2 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 54.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431858

CATALOG NUMBER: LAMR4B412R309027DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P431858

CATALOG NUMBER: LAMR4B412R309027DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	95	94	93	93	93
3	107	103	99	96	105	101	98	95	99	96	94	96	94	92	94	92	91	90	90	90
4	104	98	94	91	102	97	94	91	95	92	90	93	91	89	92	90	88	87	87	87
5	101	95	91	87	99	94	90	87	92	89	86	91	88	86	89	87	85	84	84	84
6	98	91	87	84	97	91	87	84	89	86	83	88	85	83	87	84	82	81	81	81
7	95	88	84	81	94	88	84	81	87	83	81	86	83	80	85	82	80	79	79	79
8	92	86	81	79	91	85	81	78	84	81	78	83	80	78	83	80	78	77	77	77
9	90	83	79	76	89	83	79	76	82	78	76	81	78	76	80	78	75	74	74	74
10	88	81	77	74	87	80	77	74	80	76	74	79	76	74	78	76	73	72	72	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9643251
5°	9432554
10°	8178523
15°	5069072
20°	1857867
25°	621033
30°	304849
35°	152022
40°	94291
45°	59866
50°	42600
55°	34751
60°	29899
65°	23582
70°	29139
75°	28785
80°	28697
85°	28304



TEST NUMBER: P431858

CATALOG NUMBER: LAMR4B412R309027DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1735.8	32.6
10°-20°	2620.6	49.2
20°-30°	638.9	12.0
30°-40°	175.0	3.3
40°-50°	70.4	1.3
50°-60°	37.7	0.7
60°-70°	22.5	0.4
70°-80°	17.3	0.3
80°-90°	4.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4995.3	93.9
0°-40°	5170.2	97.1
0°-60°	5278.4	99.2
0°-90°	5322.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5322.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19545	
5°	19046	###
15°	9924	2621
25°	1141	639
35°	252	175
45°	86	70
55°	40	38
65°	20	22
75°	15	17
85°	5	4
90°	0	



TEST NUMBER: P431858

CATALOG NUMBER: LAMR4B412R309027DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	19545.3
2.5°	19414.0
5°	19045.5
7.5°	18167.2
10°	16324.7
12.5°	13437.4
15°	9924.1
17.5°	6395.6
20°	3538.5
22.5°	1887.9
25°	1140.8
27.5°	772.3
30°	535.1
32.5°	363.4
35°	252.4
37.5°	186.8
40°	146.4
42.5°	111.1
45°	85.8
47.5°	70.7
50°	55.5
52.5°	50.5
55°	40.4
57.5°	35.3
60°	30.3
62.5°	25.2
65°	20.2
67.5°	20.2
70°	20.2
72.5°	20.2
75°	15.1
77.5°	15.1
80°	10.1
82.5°	5.0
85°	5.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)