

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431084

Luminaire Tested: **LAMR4B112R459730DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431084
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-908-8)
Test Lab: INNOVATION CENTER (G2)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B112R459730DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 45 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1134.9 lumens
Efficiency: N/A
Efficacy: 79.4 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.66
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431084

CATALOG NUMBER: LAMR4B112R459730DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P431084

CATALOG NUMBER: LAMR4B112R459730DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	98	93	90	95	92	89	93	90	87	90	88	86	85			
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			
6	92	85	79	76	91	84	79	75	82	78	75	81	77	74	80	77	74	73			
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69			
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66			
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	65	63			
10	79	71	66	62	78	70	66	62	70	65	62	69	65	62	68	65	62	61			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1048777
5°	1048425
10°	996521
15°	875331
20°	669641
25°	390922
30°	160030
35°	67639
40°	36905
45°	23793
50°	18575
55°	16085
60°	13025
65°	10273
70°	9521
75°	8388
80°	9376
85°	6227



TEST NUMBER: P431084

CATALOG NUMBER: LAMR4B112R459730DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	198.1	17.5
10°-20°	466.6	41.1
20°-30°	328.7	29.0
30°-40°	80.9	7.1
40°-50°	28.2	2.5
50°-60°	16.7	1.5
60°-70°	9.2	0.8
70°-80°	5.1	0.4
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	993.4	87.5
0°-40°	1074.3	94.7
0°-60°	1119.2	98.6
0°-90°	1134.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1134.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2126	
5°	2117	198
15°	1714	467
25°	718	329
35°	112	81
45°	34	28
55°	19	17
65°	9	9
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P431084

CATALOG NUMBER: LAMR4B112R459730DE010x1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2125.7
2.5°	2120.2
5°	2116.9
7.5°	2078.3
10°	1989.1
12.5°	1867.9
15°	1713.7
17.5°	1514.4
20°	1275.4
22.5°	1001.2
25°	718.1
27.5°	463.7
30°	280.9
32.5°	170.7
35°	112.3
37.5°	79.3
40°	57.3
42.5°	44.1
45°	34.1
47.5°	28.6
50°	24.2
52.5°	20.9
55°	18.7
57.5°	16.5
60°	13.2
62.5°	11.0
65°	8.8
67.5°	7.7
70°	6.6
72.5°	5.5
75°	4.4
77.5°	4.4
80°	3.3
82.5°	2.2
85°	1.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)