

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432001

Luminaire Tested: **LAMR4B412R609027DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432001
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B412R609027DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4967.9 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 54.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432001

CATALOG NUMBER: LAMR4B412R609027DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P432001

CATALOG NUMBER: LAMR4B412R609027DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82			82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77			77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72			72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	69	67			67
7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63			63
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	60	59			59
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56			56
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2817000
5°	2722566
10°	2697184
15°	2630283
20°	2427381
25°	2173780
30°	1682113
35°	1007717
40°	387145
45°	141502
50°	5526
55°	4129
60°	4736
65°	2802
70°	3462
75°	4575
80°	6819
85°	0



TEST NUMBER: P432001

CATALOG NUMBER: LAMR4B412R609027DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	522.0	10.5
10°-20°	1432.5	28.8
20°-30°	1787.2	36.0
30°-40°	1041.1	21.0
40°-50°	173.8	3.5
50°-60°	4.6	0.1
60°-70°	3.3	0.1
70°-80°	2.5	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3741.7	75.3
0°-40°	4782.8	96.3
0°-60°	4961.2	99.9
0°-90°	4967.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4967.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5710	
5°	5497	522
15°	5150	1433
25°	3993	1787
35°	1673	1041
45°	203	174
55°	5	5
65°	2	3
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P432001

CATALOG NUMBER: LAMR4B412R609027DE01021MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	5709.6
2.5°	5615.5
5°	5497.2
7.5°	5429.6
10°	5383.7
12.5°	5308.9
15°	5149.5
17.5°	4910.5
20°	4623.2
22.5°	4331.1
25°	3993.1
27.5°	3524.8
30°	2952.6
32.5°	2312.8
35°	1673.1
37.5°	1055.0
40°	601.1
42.5°	352.5
45°	202.8
47.5°	70.0
50°	7.2
52.5°	4.8
55°	4.8
57.5°	4.8
60°	4.8
62.5°	4.8
65°	2.4
67.5°	2.4
70°	2.4
72.5°	2.4
75°	2.4
77.5°	2.4
80°	2.4
82.5°	2.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)