

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430079

Luminaire Tested: **LAM4B212R209024DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430079
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-3)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B212R209024DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 20 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2033.8 lumens
Efficiency: N/A
Efficacy: 71.6 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.33
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430079

CATALOG NUMBER: LAM4B212R209024DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P430079

CATALOG NUMBER: LAM4B212R209024DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97	97	95	94	93	91	91	89	88	87	85	84	81	80														
2	112	108	105	103	110	106	104	102	103	101	100	101	99	97	98	97	95	94	93	91	91	89	88	87	85	84	81	80	78	77															
3	108	104	100	98	107	103	100	97	100	98	95	98	96	94	96	94	93	91	91	89	88	87	85	84	81	80	78	77	75	74															
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	87	87	85	84	81	80	78	77	75	74	72	71															
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	85	85	83	82	81	80	78	77	75	74	72	71															
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	83	83	81	80	78	77	75	74	72	71	69	68															
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83	81	81	79	78	77	75	74	72	71	69	68	66	65														
8	96	90	86	83	95	89	86	83	88	85	83	87	85	82	87	84	82	81	79	79	77	76	75	73	72	70	69	67	66	64	63														
9	94	88	84	81	93	87	84	81	86	83	81	86	83	81	85	82	81	80	78	78	76	75	73	72	70	69	67	66	64	63	61														
10	92	86	82	80	91	85	82	80	85	82	79	84	81	79	83	81	79	78	76	76	74	73	71	70	68	67	65	64	62	61	59														

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7025231
5°	5938118
10°	3487847
15°	1248867
20°	413209
25°	164458
30°	78619
35°	44932
40°	32461
45°	27352
50°	31470
55°	25633
60°	12927
65°	10857
70°	13416
75°	14297
80°	10513
85°	10756



TEST NUMBER: P430079

CATALOG NUMBER: LAM4B212R209024DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	981.8	48.3
10°-20°	765.6	37.6
20°-30°	158.9	7.8
30°-40°	50.1	2.5
40°-50°	32.2	1.6
50°-60°	25.9	1.3
60°-70°	10.1	0.5
70°-80°	7.6	0.4
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1906.3	93.7
0°-40°	1956.4	96.2
0°-60°	2014.5	99.1
0°-90°	2033.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2033.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14239	
5°	11990	982
15°	2445	766
25°	302	159
35°	75	50
45°	39	32
55°	30	26
65°	9	10
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P430079

CATALOG NUMBER: LAM4B212R209024DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	14239.0
2.5°	13716.8
5°	11989.8
7.5°	9606.4
10°	6961.9
12.5°	4392.0
15°	2445.0
17.5°	1344.6
20°	787.0
22.5°	481.2
25°	302.1
27.5°	199.6
30°	138.0
32.5°	97.0
35°	74.6
37.5°	59.7
40°	50.4
42.5°	42.9
45°	39.2
47.5°	39.2
50°	41.0
52.5°	39.2
55°	29.8
57.5°	20.5
60°	13.1
62.5°	11.2
65°	9.3
67.5°	9.3
70°	9.3
72.5°	9.3
75°	7.5
77.5°	5.6
80°	3.7
82.5°	1.9
85°	1.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)