

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431423

Luminaire Tested: **LAMR4B212R609024DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431423
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B212R609024DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1913.8 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431423

CATALOG NUMBER: LAMR4B212R609024DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P431423

CATALOG NUMBER: LAMR4B212R609024DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82			
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77			
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	69	67			
7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63			
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	60	59			
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1085188
5°	1048821
10°	1039055
15°	1013242
20°	935103
25°	837426
30°	647983
35°	388186
40°	149165
45°	54494
50°	2149
55°	1634
60°	1875
65°	1051
70°	1298
75°	1716
80°	2557
85°	0



TEST NUMBER: P431423

CATALOG NUMBER: LAMR4B212R609024DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.1	10.5
10°-20°	551.9	28.8
20°-30°	688.5	36.0
30°-40°	401.1	21.0
40°-50°	67.0	3.5
50°-60°	1.8	0.1
60°-70°	1.3	0.1
70°-80°	1.0	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1441.4	75.3
0°-40°	1842.5	96.3
0°-60°	1911.2	99.9
0°-90°	1913.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1913.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2200	
5°	2118	201
15°	1984	552
25°	1538	688
35°	644	401
45°	78	67
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P431423

CATALOG NUMBER: LAMR4B212R609024DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2199.5
2.5°	2163.2
5°	2117.7
7.5°	2091.6
10°	2074.0
12.5°	2045.1
15°	1983.7
17.5°	1891.7
20°	1781.0
22.5°	1668.5
25°	1538.3
27.5°	1357.8
30°	1137.4
32.5°	891.0
35°	644.5
37.5°	406.4
40°	231.6
42.5°	135.8
45°	78.1
47.5°	27.0
50°	2.8
52.5°	1.9
55°	1.9
57.5°	1.9
60°	1.9
62.5°	1.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)