

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431886

Luminaire Tested: **LAMR4B412R359030DE01021MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431886
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-908-6)
Test Lab: INNOVATION CENTER (G2)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B412R359030DE01021MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 35 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5466.4 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.57 / 0.51
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 54.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431886

CATALOG NUMBER: LAMR4B412R359030DE01021MW

Luminous Intensity Polar Plot





TEST NUMBER: P431886

CATALOG NUMBER: LAMR4B412R359030DE01021MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|---|--|--|--|--|--|--|---|--|--|--|--|--|--|--|--|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 | | | | | | | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1 | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2 | 110 | 106 | 103 | 100 | 108 | 104 | 101 | 99 | 101 | 99 | 97 | 98 | 96 | 95 | 96 | 94 | 93 | 91 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 3 | 106 | 101 | 97 | 94 | 104 | 100 | 96 | 93 | 97 | 94 | 92 | 95 | 92 | 90 | 93 | 91 | 89 | 87 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 4 | 102 | 96 | 92 | 89 | 101 | 95 | 91 | 88 | 93 | 90 | 87 | 91 | 88 | 86 | 90 | 87 | 85 | 84 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 5 | 99 | 92 | 88 | 84 | 97 | 91 | 87 | 84 | 90 | 86 | 83 | 88 | 85 | 83 | 87 | 84 | 82 | 81 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 6 | 96 | 89 | 84 | 81 | 94 | 88 | 84 | 80 | 87 | 83 | 80 | 85 | 82 | 79 | 84 | 81 | 79 | 78 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 7 | 92 | 85 | 81 | 77 | 91 | 85 | 80 | 77 | 84 | 80 | 77 | 82 | 79 | 76 | 81 | 78 | 76 | 75 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 8 | 90 | 82 | 78 | 74 | 88 | 82 | 77 | 74 | 81 | 77 | 74 | 80 | 76 | 74 | 79 | 76 | 73 | 72 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 9 | 87 | 79 | 75 | 72 | 86 | 79 | 75 | 72 | 78 | 74 | 71 | 77 | 74 | 71 | 77 | 73 | 71 | 70 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 10 | 84 | 77 | 72 | 69 | 83 | 76 | 72 | 69 | 76 | 72 | 69 | 75 | 71 | 69 | 74 | 71 | 69 | 68 | | | | | | | | | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° |
|-----|---------|
| 0° | 7822631 |
| 5° | 7642322 |
| 10° | 7032858 |
| 15° | 5083170 |
| 20° | 2511126 |
| 25° | 921207 |
| 30° | 415372 |
| 35° | 226105 |
| 40° | 140148 |
| 45° | 94893 |
| 50° | 71000 |
| 55° | 60815 |
| 60° | 53680 |
| 65° | 50783 |
| 70° | 47027 |
| 75° | 41557 |
| 80° | 46313 |
| 85° | 30569 |



TEST NUMBER: P431886

CATALOG NUMBER: LAMR4B412R359030DE01021MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 1433.8 | 26.2 |
| 10°-20° | 2620.4 | 47.9 |
| 20°-30° | 912.3 | 16.7 |
| 30°-40° | 252.8 | 4.6 |
| 40°-50° | 109.9 | 2.0 |
| 50°-60° | 63.7 | 1.2 |
| 60°-70° | 43.1 | 0.8 |
| 70°-80° | 23.7 | 0.4 |
| 80°-90° | 6.6 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 4966.6 | 90.9 |
| 0°-40° | 5219.4 | 95.5 |
| 0°-60° | 5393.0 | 98.7 |
| 0°-90° | 5466.4 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 5466.4 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 15855 | |
| 5° | 15431 | ### |
| 15° | 9952 | 2620 |
| 25° | 1692 | 912 |
| 35° | 375 | 253 |
| 45° | 136 | 110 |
| 55° | 71 | 64 |
| 65° | 44 | 43 |
| 75° | 22 | 24 |
| 85° | 5 | 7 |
| 90° | 0 | |



TEST NUMBER: P431886

CATALOG NUMBER: LAMR4B412R359030DE01021MW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 15855.2 |
| 1° | 15800.8 |
| 2° | 15719.2 |
| 3° | 15637.6 |
| 4° | 15545.1 |
| 5° | 15430.8 |
| 6° | 15289.3 |
| 7° | 15115.2 |
| 8° | 14848.6 |
| 9° | 14505.8 |
| 10° | 14037.9 |
| 11° | 13439.4 |
| 12° | 12715.7 |
| 13° | 11866.9 |
| 14° | 10936.5 |
| 15° | 9951.7 |
| 16° | 8901.6 |
| 17° | 7846.0 |
| 18° | 6785.0 |
| 19° | 5762.1 |
| 20° | 4782.7 |
| 22.5° | 2851.1 |
| 25° | 1692.2 |
| 26° | 1409.2 |
| 27° | 1175.3 |
| 28° | 995.7 |
| 29° | 848.8 |
| 30° | 729.1 |
| 32.5° | 516.9 |
| 35° | 375.4 |
| 37.5° | 282.9 |
| 40° | 217.6 |
| 42.5° | 168.7 |
| 45° | 136.0 |
| 47.5° | 114.3 |
| 50° | 92.5 |
| 52.5° | 81.6 |
| 55° | 70.7 |
| 57.5° | 59.9 |
| 60° | 54.4 |
| 62.5° | 49.0 |
| 65° | 43.5 |
| 67.5° | 38.1 |



TEST NUMBER: P431886

CATALOG NUMBER: LAMR4B412R359030DE01021MW

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|------|
| 75° | 21.8 |
| 77.5° | 16.3 |
| 80° | 16.3 |
| 82.5° | 10.9 |
| 85° | 5.4 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|------|
| 70° | | 32.6 |
| 72.5° | | 27.2 |



(END OF REPORT)