

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431283

Luminaire Tested: **LAMR4B212R309027DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431283
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B212R309027DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2217.3 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431283

CATALOG NUMBER: LAMR4B212R309027DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P431283

CATALOG NUMBER: LAMR4B212R309027DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96			96																
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	95	94	93			93																
3	107	103	99	96	105	101	98	95	99	96	94	96	94	92	94	92	91	90			90																
4	104	98	94	91	102	97	94	91	95	92	90	93	91	89	92	90	88	87			87																
5	101	95	91	87	99	94	90	87	92	89	86	91	88	86	89	87	85	84			84																
6	98	91	87	84	97	91	87	84	89	86	83	88	85	83	87	84	82	81			81																
7	95	88	84	81	94	88	84	81	87	83	81	86	83	80	85	82	80	79			79																
8	92	86	81	79	91	85	81	78	84	81	78	83	80	78	83	80	78	77			77																
9	90	83	79	76	89	83	79	76	82	78	76	81	78	76	80	78	75	74			74																
10	88	81	77	74	87	80	77	74	80	76	74	79	76	74	78	76	73	72			72																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4017540
5°	3929773
10°	3407338
15°	2111888
20°	774019
25°	258746
30°	126987
35°	63363
40°	39288
45°	24979
50°	17731
55°	14451
60°	12433
65°	9806
70°	12117
75°	12010
80°	11933
85°	11888



TEST NUMBER: P431283

CATALOG NUMBER: LAMR4B212R309027DE010x1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	723.1	32.6
10°-20°	1091.8	49.2
20°-30°	266.2	12.0
30°-40°	72.9	3.3
40°-50°	29.3	1.3
50°-60°	15.7	0.7
60°-70°	9.4	0.4
70°-80°	7.2	0.3
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2081.1	93.9
0°-40°	2154.0	97.1
0°-60°	2199.0	99.2
0°-90°	2217.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2217.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8143	
5°	7935	723
15°	4135	1092
25°	475	266
35°	105	73
45°	36	29
55°	17	16
65°	8	9
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P431283

CATALOG NUMBER: LAMR4B212R309027DE010x1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	8142.9
2.5°	8088.2
5°	7934.7
7.5°	7568.8
10°	6801.2
12.5°	5598.3
15°	4134.6
17.5°	2664.5
20°	1474.2
22.5°	786.5
25°	475.3
27.5°	321.8
30°	222.9
32.5°	151.4
35°	105.2
37.5°	77.8
40°	61.0
42.5°	46.3
45°	35.8
47.5°	29.4
50°	23.1
52.5°	21.0
55°	16.8
57.5°	14.7
60°	12.6
62.5°	10.5
65°	8.4
67.5°	8.4
70°	8.4
72.5°	8.4
75°	6.3
77.5°	6.3
80°	4.2
82.5°	2.1
85°	2.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)