

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430881

Luminaire Tested: **LAM4B412R659035DE01021MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430881
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-908-22)
Test Lab: INNOVATION CENTER (G2)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B412R659035DE01021MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 65 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5751.8 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.97
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 54.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430881

CATALOG NUMBER: LAM4B412R659035DE01021MW

Luminous Intensity Polar Plot





TEST NUMBER: P430881

CATALOG NUMBER: LAM4B412R659035DE01021MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	72	72	72	72
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	68	67	67	67	67
6	85	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54	54	54	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50	50	50	50
10	69	59	53	49	68	58	53	49	58	52	48	57	52	48	56	51	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2739194
5°	2628565
10°	2566325
15°	2494670
20°	2323213
25°	2145853
30°	1926289
35°	1415176
40°	764307
45°	328707
50°	183064
55°	128253
60°	82394
65°	62691
70°	51643
75°	45560
80°	50859
85°	33965



TEST NUMBER: P430881

CATALOG NUMBER: LAM4B412R659035DE01021MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	501.6	8.7
10°-20°	1362.8	23.7
20°-30°	1806.6	31.4
30°-40°	1430.6	24.9
40°-50°	426.1	7.4
50°-60°	136.4	2.4
60°-70°	54.5	0.9
70°-80°	26.0	0.5
80°-90°	7.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3670.9	63.8
0°-40°	5101.6	88.7
0°-60°	5664.1	98.5
0°-90°	5751.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5751.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5552	
5°	5307	502
15°	4884	1363
25°	3942	1807
35°	2350	1431
45°	471	426
55°	149	136
65°	54	54
75°	24	26
85°	6	7
90°	0	



TEST NUMBER: P430881

CATALOG NUMBER: LAM4B412R659035DE01021MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5551.9
1°	5516.1
2°	5462.4
3°	5402.8
4°	5349.1
5°	5307.4
6°	5277.6
7°	5247.7
8°	5200.0
9°	5158.3
10°	5122.5
11°	5080.8
12°	5033.1
13°	4991.3
14°	4943.6
15°	4884.0
16°	4818.4
17°	4734.9
18°	4639.5
19°	4538.1
20°	4424.8
21°	4317.5
22°	4204.2
23°	4102.8
24°	4019.3
25°	3941.8
26°	3858.3
27°	3774.8
28°	3667.5
29°	3536.3
30°	3381.2
32.5°	2910.1
35°	2349.6
37.5°	1741.3
40°	1186.7
42.5°	751.4
45°	471.1
47.5°	316.1
50°	238.5
52.5°	190.8
55°	149.1
57.5°	113.3
60°	83.5



TEST NUMBER: P430881

CATALOG NUMBER: LAM4B412R659035DE01021MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	41.7
70°	35.8
72.5°	29.8
75°	23.9
77.5°	17.9
80°	17.9
82.5°	11.9
85°	6.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







62.5°		65.6
65°		53.7



(END OF REPORT)