

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431475

Luminaire Tested: **LAMR4B212R709027DE010x1MW**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P431475  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B212R709027DE010x1MW  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2129.6 lumens  
Efficiency: N/A  
Efficacy: 75.0 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 28.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P431475

CATALOG NUMBER: LAMR4B212R709027DE010x1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P431475

CATALOG NUMBER: LAMR4B212R709027DE010x1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			92																
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84			84																
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			76																
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70																
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64			64																
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	64	60	58			58																
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54			54																
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50			50																
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46			46																
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	48	44	43			43																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	772287
5°	757952
10°	766716
15°	788395
20°	789718
25°	716464
30°	640178
35°	562252
40°	413938
45°	231860
50°	114137
55°	63911
60°	38878
65°	25567
70°	18897
75°	16585
80°	12502
85°	12454



TEST NUMBER: P431475

CATALOG NUMBER: LAMR4B212R709027DE010x1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	146.3	6.9
10°-20°	434.9	20.4
20°-30°	603.6	28.3
30°-40°	567.9	26.7
40°-50°	271.1	12.7
50°-60°	71.7	3.4
60°-70°	22.6	1.1
70°-80°	9.2	0.4
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1184.8	55.6
0°-40°	1752.6	82.3
0°-60°	2095.4	98.4
0°-90°	2129.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2129.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1565	
5°	1530	146
15°	1544	435
25°	1316	604
35°	934	568
45°	332	271
55°	74	72
65°	22	23
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P431475

CATALOG NUMBER: LAMR4B212R709027DE010x1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1565.3
2.5°	1545.7
5°	1530.4
7.5°	1528.2
10°	1530.4
12.5°	1534.7
15°	1543.5
17.5°	1543.5
20°	1504.1
22.5°	1421.0
25°	1316.1
27.5°	1211.2
30°	1123.7
32.5°	1038.5
35°	933.5
37.5°	798.0
40°	642.7
42.5°	478.8
45°	332.3
47.5°	220.8
50°	148.7
52.5°	102.8
55°	74.3
57.5°	52.5
60°	39.4
62.5°	28.4
65°	21.9
67.5°	15.3
70°	13.1
72.5°	10.9
75°	8.7
77.5°	6.6
80°	4.4
82.5°	4.4
85°	2.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)