

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432009

Luminaire Tested: **LAMR4B412R609035DE01021MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B412R609035DE01021MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5627.2 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 54.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432009

CATALOG NUMBER: LAMR4B412R609035DE01021MW

Luminous Intensity Polar Plot





TEST NUMBER: P432009

CATALOG NUMBER: LAMR4B412R609035DE01021MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94																																				
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																																				
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82																																				
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77																																				
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72																																				
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	69	67																																				
7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63																																				
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	60	59																																				
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56																																				
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3190834
5°	3083812
10°	3055092
15°	2979353
20°	2749496
25°	2462249
30°	1905324
35°	1141429
40°	438541
45°	160272
50°	6294
55°	4731
60°	5427
65°	3152
70°	3895
75°	5147
80°	7671
85°	0



TEST NUMBER: P432009

CATALOG NUMBER: LAMR4B412R609035DE01021MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	591.3	10.5
10°-20°	1622.6	28.8
20°-30°	2024.3	36.0
30°-40°	1179.3	21.0
40°-50°	196.8	3.5
50°-60°	5.2	0.1
60°-70°	3.7	0.1
70°-80°	2.9	0.1
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4238.2	75.3
0°-40°	5417.5	96.3
0°-60°	5619.6	99.9
0°-90°	5627.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5627.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6467	
5°	6227	591
15°	5833	1623
25°	4523	2024
35°	1895	1179
45°	230	197
55°	6	5
65°	3	4
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P432009

CATALOG NUMBER: LAMR4B412R609035DE01021MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6467.3
2.5°	6360.6
5°	6226.6
7.5°	6150.1
10°	6098.1
12.5°	6013.3
15°	5832.9
17.5°	5562.1
20°	5236.7
22.5°	4905.8
25°	4523.0
27.5°	3992.5
30°	3344.4
32.5°	2619.7
35°	1895.1
37.5°	1195.0
40°	680.9
42.5°	399.2
45°	229.7
47.5°	79.3
50°	8.2
52.5°	5.5
55°	5.5
57.5°	5.5
60°	5.5
62.5°	5.5
65°	2.7
67.5°	2.7
70°	2.7
72.5°	2.7
75°	2.7
77.5°	2.7
80°	2.7
82.5°	2.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)