

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430086

Luminaire Tested: **LAM4B212R209030DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430086
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-3)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B212R209030DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 20 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2305.6 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.33
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430086

CATALOG NUMBER: LAM4B212R209030DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P430086

CATALOG NUMBER: LAM4B212R209030DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97			97																
2	112	108	105	103	110	106	104	102	103	101	100	101	99	97	98	97	95			94																	
3	108	104	100	98	107	103	100	97	100	98	95	98	96	94	96	94	93			91																	
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90			89																	
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88			87																	
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86			85																	
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84			83																	
8	96	90	86	83	95	89	86	83	88	85	83	87	85	82	87	84	82			81																	
9	94	88	84	81	93	87	84	81	86	83	81	86	83	81	85	82	81			80																	
10	92	86	82	80	91	85	82	80	85	82	79	84	81	79	83	81	79			78																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7964133
5°	6731779
10°	3954019
15°	1415740
20°	468444
25°	186452
30°	89159
35°	50955
40°	36776
45°	30980
50°	35692
55°	29074
60°	14604
65°	12375
70°	15291
75°	16203
80°	11933
85°	11888



TEST NUMBER: P430086

CATALOG NUMBER: LAM4B212R209030DE010x1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1113.0	48.3
10°-20°	867.9	37.6
20°-30°	180.1	7.8
30°-40°	56.8	2.5
40°-50°	36.5	1.6
50°-60°	29.3	1.3
60°-70°	11.5	0.5
70°-80°	8.6	0.4
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2161.1	93.7
0°-40°	2217.9	96.2
0°-60°	2283.7	99.1
0°-90°	2305.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2305.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16142	
5°	13592	###
15°	2772	868
25°	342	180
35°	85	57
45°	44	37
55°	34	29
65°	11	12
75°	8	9
85°	2	2
90°	0	



TEST NUMBER: P430086

CATALOG NUMBER: LAM4B212R209030DE010x1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	16142.0
2.5°	15550.1
5°	13592.3
7.5°	10890.3
10°	7892.4
12.5°	4979.0
15°	2771.7
17.5°	1524.4
20°	892.2
22.5°	545.5
25°	342.5
27.5°	226.2
30°	156.5
32.5°	109.9
35°	84.6
37.5°	67.7
40°	57.1
42.5°	48.6
45°	44.4
47.5°	44.4
50°	46.5
52.5°	44.4
55°	33.8
57.5°	23.3
60°	14.8
62.5°	12.7
65°	10.6
67.5°	10.6
70°	10.6
72.5°	10.6
75°	8.5
77.5°	6.3
80°	4.2
82.5°	2.1
85°	2.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)