

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430087

Luminaire Tested: **LAM4B212R209035DE010x1MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430087
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-3)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B212R209035DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 20 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2491.4 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.33
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430087

CATALOG NUMBER: LAM4B212R209035DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P430087

CATALOG NUMBER: LAM4B212R209035DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97	97	95	94	93	91	91	89	88	87	87	85	85	83	83	81	81	80	80									
2	112	108	105	103	110	106	104	102	103	101	100	101	99	97	98	97	95	94	93	91	91	89	88	87	87	85	85	83	83	81	81	80	80												
3	108	104	100	98	107	103	100	97	100	98	95	98	96	94	96	94	93	91	91	89	88	87	87	85	85	83	83	81	81	80	80														
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	87	87	85	85	83	83	81	81	80	80																	
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	85	85	83	83	81	81	80	80																			
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	83	83	81	81	80	80																					
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83	81	81	80	80																							
8	96	90	86	83	95	89	86	83	88	85	83	87	85	82	87	84	82	81	80	80																									
9	94	88	84	81	93	87	84	81	86	83	81	86	83	81	85	82	81	80	80																										
10	92	86	82	80	91	85	82	80	85	82	79	84	81	79	83	81	79	78	78																										

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8605871
5°	7274193
10°	4272599
15°	1529849
20°	506194
25°	201477
30°	96337
35°	55051
40°	39739
45°	33492
50°	38608
55°	31483
60°	15788
65°	13309
70°	16445
75°	17347
80°	13070
85°	13020



TEST NUMBER: P430087

CATALOG NUMBER: LAM4B212R209035DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1202.7	48.3
10°-20°	937.9	37.6
20°-30°	194.7	7.8
30°-40°	61.4	2.5
40°-50°	39.5	1.6
50°-60°	31.7	1.3
60°-70°	12.4	0.5
70°-80°	9.3	0.4
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2335.2	93.7
0°-40°	2396.6	96.2
0°-60°	2467.8	99.1
0°-90°	2491.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2491.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17443	
5°	14688	###
15°	2995	938
25°	370	195
35°	91	61
45°	48	39
55°	37	32
65°	11	12
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P430087

CATALOG NUMBER: LAM4B212R209035DE010x1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	17442.7
2.5°	16803.0
5°	14687.5
7.5°	11767.8
10°	8528.3
12.5°	5380.2
15°	2995.1
17.5°	1647.2
20°	964.1
22.5°	589.4
25°	370.1
27.5°	244.4
30°	169.1
32.5°	118.8
35°	91.4
37.5°	73.1
40°	61.7
42.5°	52.5
45°	48.0
47.5°	48.0
50°	50.3
52.5°	48.0
55°	36.6
57.5°	25.1
60°	16.0
62.5°	13.7
65°	11.4
67.5°	11.4
70°	11.4
72.5°	11.4
75°	9.1
77.5°	6.9
80°	4.6
82.5°	2.3
85°	2.3
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)