

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431823

Luminaire Tested: **LAMR4B412R209050DE01021MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431823
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-3)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B412R209050DE01021MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 20 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5881.5 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.33
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 54.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431823

CATALOG NUMBER: LAMR4B412R209050DE01021MW

Luminous Intensity Polar Plot





TEST NUMBER: P431823

CATALOG NUMBER: LAMR4B412R209050DE01021MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97				97															
2	112	108	105	103	110	106	104	102	103	101	100	101	99	97	98	97	95				94																
3	108	104	100	98	107	103	100	97	100	98	95	98	96	94	96	94	93				91																
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90				89																
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88				87																
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86				85																
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84				83																
8	96	90	86	83	95	89	86	83	88	85	83	87	85	82	87	84	82				81																
9	94	88	84	81	93	87	84	81	86	83	81	86	83	81	85	82	81				80																
10	92	86	82	80	91	85	82	80	85	82	79	84	81	79	83	81	79				78																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20315988
5°	17172295
10°	10086396
15°	3611499
20°	1194947
25°	475628
30°	227370
35°	129917
40°	93775
45°	79054
50°	91110
55°	74234
60°	37299
65°	31521
70°	38949
75°	41175
80°	30686
85°	30569



TEST NUMBER: P431823

CATALOG NUMBER: LAMR4B412R209050DE01021MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2839.1	48.3
10°-20°	2214.1	37.6
20°-30°	459.5	7.8
30°-40°	144.9	2.5
40°-50°	93.2	1.6
50°-60°	74.8	1.3
60°-70°	29.4	0.5
70°-80°	22.1	0.4
80°-90°	4.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5512.7	93.7
0°-40°	5657.6	96.2
0°-60°	5825.6	99.0
0°-90°	5881.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5881.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	41177	
5°	34673	###
15°	7070	2214
25°	874	460
35°	216	145
45°	113	93
55°	86	75
65°	27	29
75°	22	22
85°	5	4
90°	0	



TEST NUMBER: P431823

CATALOG NUMBER: LAMR4B412R209050DE01021MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	41177.2
2.5°	39667.1
5°	34673.0
7.5°	27780.5
10°	20132.9
12.5°	12701.0
15°	7070.5
17.5°	3888.5
20°	2275.9
22.5°	1391.4
25°	873.7
27.5°	577.1
30°	399.1
32.5°	280.4
35°	215.7
37.5°	172.6
40°	145.6
42.5°	124.0
45°	113.3
47.5°	113.3
50°	118.7
52.5°	113.3
55°	86.3
57.5°	59.3
60°	37.8
62.5°	32.4
65°	27.0
67.5°	27.0
70°	27.0
72.5°	27.0
75°	21.6
77.5°	16.2
80°	10.8
82.5°	5.4
85°	5.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)