

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432015

Luminaire Tested: **LAMR4B412R609050DE01021MW**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P432015  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B412R609050DE01021MW  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5534.6 lumens  
Efficiency: N/A  
Efficacy: 102.3 lumens/watt  
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 54.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P432015

CATALOG NUMBER: LAMR4B412R609050DE01021MW

### Luminous Intensity Polar Plot





TEST NUMBER: P432015

CATALOG NUMBER: LAMR4B412R609050DE01021MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100																
	1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94	94	94	94	94	94	94	94	94																
	2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88	88	88	88	88	88	88	88	88	88															
	3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82	82	82	82	82	82	82	82	82	82	82	82	82															
	4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77	77	77	77	77	77	77	77	77	77															
	5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72	72	72	72	72	72	72	72	72	72															
	6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	69	67	67	67	67	67	67	67	67	67	67	67	67	67															
	7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63	63	63	63	63	63	63	63	63	63															
	8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	60	59	59	59	59	59	59	59	59	59	59	59	59	59															
	9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56	56	56	56	56	56	56	56	56	56	56	56	56															
	10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53	53	53	53	53	53	53	53	53	53															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3138239
5°	3032998
10°	3004742
15°	2930215
20°	2704184
25°	2421638
30°	1873933
35°	1122576
40°	431328
45°	157620
50°	6217
55°	4645
60°	5328
65°	3152
70°	3895
75°	5147
80°	7671
85°	0



TEST NUMBER: P432015

CATALOG NUMBER: LAMR4B412R609050DE01021MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	581.5	10.5
10°-20°	1595.9	28.8
20°-30°	1990.9	36.0
30°-40°	1159.8	21.0
40°-50°	193.6	3.5
50°-60°	5.1	0.1
60°-70°	3.7	0.1
70°-80°	2.9	0.1
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4168.4	75.3
0°-40°	5328.2	96.3
0°-60°	5526.9	99.9
0°-90°	5534.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5534.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6361	
5°	6124	582
15°	5737	1596
25°	4448	1991
35°	1864	1160
45°	226	194
55°	5	5
65°	3	4
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P432015

CATALOG NUMBER: LAMR4B412R609050DE01021MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6360.7
2.5°	6255.8
5°	6124.0
7.5°	6048.7
10°	5997.6
12.5°	5914.2
15°	5736.7
17.5°	5470.5
20°	5150.4
22.5°	4825.0
25°	4448.4
27.5°	3926.7
30°	3289.3
32.5°	2576.5
35°	1863.8
37.5°	1175.3
40°	669.7
42.5°	392.7
45°	225.9
47.5°	78.0
50°	8.1
52.5°	5.4
55°	5.4
57.5°	5.4
60°	5.4
62.5°	5.4
65°	2.7
67.5°	2.7
70°	2.7
72.5°	2.7
75°	2.7
77.5°	2.7
80°	2.7
82.5°	2.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)