

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431265

Luminaire Tested: **LAMR4B212R259035DE010x1MW**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P431265  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-5)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B212R259035DE010x1MW  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 25 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2523.8 lumens  
Efficiency: N/A  
Efficacy: 88.9 lumens/watt  
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41  
Luminous Opening: Circular (Dia: 0.29' x H: 0')  
CIE Type: Direct


Input Watts (W): 28.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P431265

CATALOG NUMBER: LAMR4B212R259035DE010x1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P431265

CATALOG NUMBER: LAMR4B212R259035DE010x1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	95
2	112	109	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	93	92
3	109	104	101	99	107	103	100	98	101	98	96	99	96	95	96	95	93	92	92	90	88
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	94	93	91	90	89	88	85
5	103	98	94	91	102	97	93	91	95	92	90	94	91	89	92	90	89	88	86	84	83
6	100	95	91	88	99	94	91	88	93	90	87	92	89	87	91	88	86	85	84	82	81
7	98	92	88	86	97	92	88	86	91	87	85	90	87	85	89	86	84	83	82	81	80
8	96	90	86	83	95	89	86	83	88	85	83	88	85	83	87	84	82	81	80	79	78
9	94	88	84	81	93	87	84	81	86	83	81	86	83	81	85	82	81	80	79	78	77
10	91	85	82	79	91	85	82	79	84	81	79	84	81	79	83	81	79	78	77	76	75

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1986313
5°	1852170
10°	1466625
15°	738116
20°	236849
25°	82835
30°	27737
35°	5566
40°	1830
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P431265

CATALOG NUMBER: LAMR4B212R259035DE010x1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1014.0	40.2
10°-20°	1229.9	48.7
20°-30°	250.3	9.9
30°-40°	28.3	1.1
40°-50°	1.4	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2494.1	98.8
0°-40°	2522.4	99.9
0°-60°	2523.8	100.0
0°-90°	2523.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2523.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12329	
5°	11453	###
15°	4426	1230
25°	466	250
35°	28	28
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P431265

CATALOG NUMBER: LAMR4B212R259035DE010x1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	12329.4
2.5°	12090.9
5°	11453.0
7.5°	10400.2
10°	8965.3
12.5°	6909.9
15°	4425.5
17.5°	2493.1
20°	1381.5
22.5°	787.1
25°	466.0
27.5°	278.7
30°	149.1
32.5°	65.3
35°	28.3
37.5°	17.4
40°	8.7
42.5°	3.3
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)