

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432061

Luminaire Tested: **LAMR4B412R709050DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B412R709050DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5694.4 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 54.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432061

CATALOG NUMBER: LAMR4B412R709050DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P432061

CATALOG NUMBER: LAMR4B412R709050DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|---|--|--|--|--|--|--|---|--|--|--|--|--|--|--|--|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 | | | | | | | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2 | 106 | 101 | 96 | 92 | 104 | 99 | 95 | 91 | 96 | 92 | 89 | 93 | 90 | 87 | 90 | 88 | 86 | 84 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 3 | 100 | 93 | 87 | 83 | 98 | 91 | 86 | 82 | 89 | 84 | 81 | 86 | 82 | 79 | 84 | 81 | 78 | 76 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 4 | 94 | 85 | 79 | 74 | 92 | 84 | 78 | 74 | 82 | 77 | 73 | 80 | 76 | 72 | 78 | 74 | 71 | 70 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 5 | 88 | 79 | 72 | 68 | 87 | 78 | 72 | 67 | 76 | 71 | 67 | 74 | 70 | 66 | 73 | 69 | 65 | 64 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 6 | 83 | 73 | 66 | 62 | 82 | 72 | 66 | 61 | 71 | 65 | 61 | 69 | 64 | 60 | 68 | 64 | 60 | 58 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 7 | 78 | 68 | 61 | 56 | 77 | 67 | 61 | 56 | 66 | 60 | 56 | 65 | 59 | 56 | 63 | 59 | 55 | 54 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 8 | 74 | 63 | 57 | 52 | 73 | 63 | 56 | 52 | 62 | 56 | 52 | 60 | 55 | 51 | 59 | 55 | 51 | 50 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 9 | 70 | 59 | 53 | 48 | 69 | 59 | 52 | 48 | 58 | 52 | 48 | 57 | 51 | 48 | 56 | 51 | 47 | 46 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 10 | 66 | 55 | 49 | 45 | 65 | 55 | 49 | 44 | 54 | 48 | 44 | 53 | 48 | 44 | 52 | 48 | 44 | 43 | | | | | | | | | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 2065139 |
| 5° | 2026671 |
| 10° | 2050104 |
| 15° | 2108108 |
| 20° | 2111725 |
| 25° | 1915797 |
| 30° | 1711851 |
| 35° | 1503474 |
| 40° | 1106948 |
| 45° | 620015 |
| 50° | 305106 |
| 55° | 171004 |
| 60° | 103807 |
| 65° | 68295 |
| 70° | 50633 |
| 75° | 44607 |
| 80° | 33243 |
| 85° | 32833 |



TEST NUMBER: P432061

CATALOG NUMBER: LAMR4B412R709050DE01021MB

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 391.2 | 6.9 |
| 10°-20° | 1163.0 | 20.4 |
| 20°-30° | 1613.9 | 28.3 |
| 30°-40° | 1518.4 | 26.7 |
| 40°-50° | 724.9 | 12.7 |
| 50°-60° | 191.6 | 3.4 |
| 60°-70° | 60.5 | 1.1 |
| 70°-80° | 24.6 | 0.4 |
| 80°-90° | 6.3 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 3168.0 | 55.6 |
| 0°-40° | 4686.5 | 82.3 |
| 0°-60° | 5602.9 | 98.4 |
| 0°-90° | 5694.4 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 5694.4 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4186 | |
| 5° | 4092 | 391 |
| 15° | 4127 | 1163 |
| 25° | 3519 | 1614 |
| 35° | 2496 | 1518 |
| 45° | 889 | 725 |
| 55° | 199 | 192 |
| 65° | 58 | 60 |
| 75° | 23 | 25 |
| 85° | 6 | 6 |
| 90° | 0 | |



TEST NUMBER: P432061

CATALOG NUMBER: LAMR4B412R709050DE01021MB

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 4185.7 |
| 2.5° | 4133.0 |
| 5° | 4092.1 |
| 7.5° | 4086.3 |
| 10° | 4092.1 |
| 12.5° | 4103.8 |
| 15° | 4127.2 |
| 17.5° | 4127.2 |
| 20° | 4022.0 |
| 22.5° | 3799.8 |
| 25° | 3519.2 |
| 27.5° | 3238.6 |
| 30° | 3004.8 |
| 32.5° | 2776.8 |
| 35° | 2496.2 |
| 37.5° | 2133.8 |
| 40° | 1718.7 |
| 42.5° | 1280.3 |
| 45° | 888.6 |
| 47.5° | 590.4 |
| 50° | 397.5 |
| 52.5° | 274.8 |
| 55° | 198.8 |
| 57.5° | 140.3 |
| 60° | 105.2 |
| 62.5° | 76.0 |
| 65° | 58.5 |
| 67.5° | 40.9 |
| 70° | 35.1 |
| 72.5° | 29.2 |
| 75° | 23.4 |
| 77.5° | 17.5 |
| 80° | 11.7 |
| 82.5° | 11.7 |
| 85° | 5.8 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)