

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431872

Luminaire Tested: **LAMR4B412R309727DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431872
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B412R309727DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5067.9 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 54.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431872

CATALOG NUMBER: LAMR4B412R309727DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P431872

CATALOG NUMBER: LAMR4B412R309727DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	95	94	93
3	107	103	99	96	105	101	98	95	99	96	94	96	94	92	94	92	91	90
4	104	98	94	91	102	97	94	91	95	92	90	93	91	89	92	90	88	87
5	101	95	91	87	99	94	90	87	92	89	86	91	88	86	89	87	85	84
6	98	91	87	84	97	91	87	84	89	86	83	88	85	83	87	84	82	81
7	95	88	84	81	94	88	84	81	87	83	81	86	83	80	85	82	80	79
8	92	86	81	79	91	85	81	78	84	81	78	83	80	78	83	80	78	77
9	90	83	79	76	89	83	79	76	82	78	76	81	78	76	80	78	75	74
10	88	81	77	74	87	80	77	74	80	76	74	79	76	74	78	76	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9182385
5°	8981814
10°	7787700
15°	4826808
20°	1769082
25°	591364
30°	290265
35°	144734
40°	89782
45°	57006
50°	40604
55°	33117
60°	28419
65°	22415
70°	27697
75°	27450
80°	27276
85°	27172



TEST NUMBER: P431872

CATALOG NUMBER: LAMR4B412R309727DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1652.8	32.6
10°-20°	2495.3	49.2
20°-30°	608.4	12.0
30°-40°	166.6	3.3
40°-50°	67.1	1.3
50°-60°	35.9	0.7
60°-70°	21.4	0.4
70°-80°	16.5	0.3
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4756.6	93.9
0°-40°	4923.1	97.1
0°-60°	5026.1	99.2
0°-90°	5067.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5067.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18611	
5°	18135	###
15°	9450	2495
25°	1086	608
35°	240	167
45°	82	67
55°	38	36
65°	19	21
75°	14	16
85°	5	4
90°	0	



TEST NUMBER: P431872

CATALOG NUMBER: LAMR4B412R309727DE01021MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	18611.2
2.5°	18486.3
5°	18135.4
7.5°	17299.0
10°	15544.6
12.5°	12795.2
15°	9449.8
17.5°	6090.0
20°	3369.4
22.5°	1797.7
25°	1086.3
27.5°	735.4
30°	509.5
32.5°	346.1
35°	240.3
37.5°	177.8
40°	139.4
42.5°	105.7
45°	81.7
47.5°	67.3
50°	52.9
52.5°	48.1
55°	38.5
57.5°	33.6
60°	28.8
62.5°	24.0
65°	19.2
67.5°	19.2
70°	19.2
72.5°	19.2
75°	14.4
77.5°	14.4
80°	9.6
82.5°	4.8
85°	4.8
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)