

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430332

Luminaire Tested: **LAM4B212R709040DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430332
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B212R709040DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2438.6 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430332

CATALOG NUMBER: LAM4B212R709040DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P430332

CATALOG NUMBER: LAM4B212R709040DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92																			
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84																			
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76																			
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70																			
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64																			
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	64	60	58																			
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54																			
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50																			
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46																			
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	48	44	43																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	884383
5°	867950
10°	877986
15°	902811
20°	904335
25°	820441
30°	733097
35°	643864
40°	474029
45°	265492
50°	130639
55°	73201
60°	44503
65°	29186
70°	21638
75°	19063
80°	14206
85°	14152



TEST NUMBER: P430332

CATALOG NUMBER: LAM4B212R709040DE010x1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.5	6.9
10°-20°	498.0	20.4
20°-30°	691.2	28.3
30°-40°	650.3	26.7
40°-50°	310.4	12.7
50°-60°	82.1	3.4
60°-70°	25.9	1.1
70°-80°	10.5	0.4
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1356.7	55.6
0°-40°	2007.0	82.3
0°-60°	2399.5	98.4
0°-90°	2438.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2438.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1792	
5°	1752	168
15°	1768	498
25°	1507	691
35°	1069	650
45°	380	310
55°	85	82
65°	25	26
75°	10	11
85°	2	3
90°	0	



TEST NUMBER: P430332

CATALOG NUMBER: LAM4B212R709040DE010x1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1792.5
2.5°	1770.0
5°	1752.5
7.5°	1750.0
10°	1752.5
12.5°	1757.5
15°	1767.5
17.5°	1767.5
20°	1722.4
22.5°	1627.3
25°	1507.1
27.5°	1387.0
30°	1286.8
32.5°	1189.2
35°	1069.0
37.5°	913.8
40°	736.0
42.5°	548.3
45°	380.5
47.5°	252.9
50°	170.2
52.5°	117.7
55°	85.1
57.5°	60.1
60°	45.1
62.5°	32.5
65°	25.0
67.5°	17.5
70°	15.0
72.5°	12.5
75°	10.0
77.5°	7.5
80°	5.0
82.5°	5.0
85°	2.5
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)