

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778278

Luminaire Tested: LERS4D15D010-EC4DR250215IC9024-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P778278
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS4D15D010-EC4DR250215IC9024-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1157.0 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P778278

CATALOG NUMBER: LERS4D15D010-EC4DR250215IC9024-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P778278

CATALOG NUMBER: LERS4D15D010-EC4DR250215IC9024-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109	112	110	109	107		106	105	104		103	102	101		99	99	98
2	111	107	104	101	109	105	102	100		102	100	98		99	97	96		97	95	94
3	107	102	98	95	105	101	97	94		98	95	93		96	93	91		94	92	90
4	103	97	93	90	102	96	93	90		94	91	89		93	90	88		91	89	87
5	100	93	89	86	98	93	89	86		91	87	85		89	86	84		88	85	83
6	97	90	85	82	95	89	85	82		88	84	81		87	83	81		85	83	80
7	93	87	82	79	92	86	82	79		85	81	78		84	80	78		83	80	78
8	91	84	79	76	90	83	79	76		82	78	76		81	78	75		80	77	75
9	88	81	76	73	87	80	76	73		80	76	73		79	75	73		78	75	73
10	85	78	74	71	85	78	74	71		77	73	71		76	73	71		76	73	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	479458
5°	446554
10°	318538
15°	187613
20°	116726
25°	64063
30°	29295
35°	11097
40°	5021
45°	3013
50°	1258
55°	800
60°	568
65°	388
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3013 cd/sqm



TEST NUMBER: P778278

CATALOG NUMBER: LERS4D15D010-EC4DR250215IC9024-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.9	30.2
10°-20°	473.9	41.0
20°-30°	250.8	21.7
30°-40°	61.9	5.4
40°-50°	15.1	1.3
50°-60°	4.0	0.3
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1074.6	92.9
0°-40°	1136.6	98.2
0°-60°	1155.6	99.9
0°-90°	1157.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1157.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4388	
5°	4072	350
15°	1659	474
25°	531	251
35°	83	62
45°	20	15
55°	4	4
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P778278

CATALOG NUMBER: LERS4D15D010-EC4DR250215IC9024-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4388.2
2.5°	4316.1
5°	4071.5
7.5°	3580.1
10°	2871.1
12.5°	2170.4
15°	1658.6
17.5°	1292.6
20°	1003.9
22.5°	752.9
25°	531.4
27.5°	356.4
30°	232.2
32.5°	141.3
35°	83.2
37.5°	50.9
40°	35.2
42.5°	26.9
45°	19.5
47.5°	11.8
50°	7.4
52.5°	5.3
55°	4.2
57.5°	3.3
60°	2.6
62.5°	2.0
65°	1.5
67.5°	0.6
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)