

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211117

Luminaire Tested: **LE_4B15D010 EC4B10208027 4L1BWH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211117
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208027 4L1BWH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1387.2 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211117

CATALOG NUMBER: LE_4B15D010 EC4B10208027 4L1BWH

Luminous Intensity Polar Plot





TEST NUMBER: P211117

CATALOG NUMBER: LE_4B15D010 EC4B10208027 4L1BWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211117

CATALOG NUMBER: LE_4B15D010 EC4B10208027 4L1BWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	6.1
10°-20°	245.4	17.7
20°-30°	362.1	26.1
30°-40°	357.3	25.8
40°-50°	218.6	15.8
50°-60°	83.8	6.0
60°-70°	26.2	1.9
70°-80°	7.6	0.6
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	692.6	49.9
0°-40°	1049.9	75.7
0°-60°	1352.4	97.5
0°-90°	1387.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1387.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	894	
5°	894	85
15°	870	245
25°	792	362
35°	580	357
45°	280	219
55°	88	84
65°	24	26
75°	8	8
85°	0	1
90°	0	



TEST NUMBER: P211117

CATALOG NUMBER: LE_4B15D010 EC4B10208027 4L1BWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	894.1
2.5°	896.0
5°	894.1
7.5°	892.3
10°	886.6
12.5°	879.0
15°	869.7
17.5°	858.4
20°	841.5
22.5°	822.6
25°	792.5
27.5°	754.8
30°	707.8
32.5°	649.5
35°	579.8
37.5°	502.6
40°	423.5
42.5°	350.1
45°	280.5
47.5°	218.3
50°	165.6
52.5°	122.4
55°	88.5
57.5°	62.2
60°	45.1
62.5°	33.9
65°	24.5
67.5°	18.8
70°	13.2
72.5°	9.4
75°	7.5
77.5°	3.7
80°	3.7
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)