

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430195

Luminaire Tested: **LAM4B212R409730DE010x1MB**

Issue Date: 11/23/2020


Test Information

Test Method: LM-41-14
Report Number: P430195
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-7)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B212R409730DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 40 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2362.1 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430195

CATALOG NUMBER: LAM4B212R409730DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P430195

CATALOG NUMBER: LAM4B212R409730DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89			
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	86			
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82			
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79			
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77			
8	91	83	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	79	75	73	79	75	73	78	75	72	71			
10	85	78	73	71	84	77	73	70	77	73	70	76	73	70	75	72	70	69			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	890501
5°	895035
10°	888681
15°	801728
20°	505826
25°	182167
30°	38173
35°	11604
40°	2313
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P430195

CATALOG NUMBER: LAM4B212R409730DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	524.8	22.2
10°-20°	1254.9	53.1
20°-30°	535.1	22.7
30°-40°	45.9	1.9
40°-50°	1.4	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2314.9	98.0
0°-40°	2360.7	99.9
0°-60°	2362.1	100.0
0°-90°	2362.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2362.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5528	
5°	5534	525
15°	4807	1255
25°	1025	535
35°	59	46
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P430195

CATALOG NUMBER: LAM4B212R409730DE010x1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	5527.5
2.5°	5522.5
5°	5534.5
7.5°	5501.5
10°	5432.4
12.5°	5226.3
15°	4806.9
17.5°	3988.3
20°	2950.4
22.5°	1942.6
25°	1024.8
27.5°	415.3
30°	205.2
32.5°	109.1
35°	59.0
37.5°	30.0
40°	11.0
42.5°	2.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)