

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211152

Luminaire Tested: **LE\_4B15D010 EC4B10209727 4LBCS1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211152  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B15D010 EC4B10209727 4LBCS1MW  
Description: PORTFOLIO 4 INCH CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM  
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W  
DL3-15.28W DLE-15.432W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1292.4 lumens  
Efficiency: N/A  
Efficacy: 90.4 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211152

CATALOG NUMBER: LE\_4B15D010 EC4B10209727 4LBCS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P211152

CATALOG NUMBER: LE\_4B15D010 EC4B10209727 4LBCS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|--|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |  |  |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |  |  |   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |  |  |   |
| 1   | 110 | 106 | 102 | 99  | 108 | 104 | 100 | 97  | 100 | 97  | 94  | 96  | 93  | 91  | 92  | 90  | 89  | 87  |  |  |   |
| 2   | 101 | 94  | 87  | 82  | 99  | 92  | 86  | 81  | 88  | 84  | 79  | 85  | 81  | 78  | 82  | 79  | 76  | 74  |  |  |   |
| 3   | 93  | 83  | 75  | 70  | 90  | 81  | 74  | 69  | 79  | 73  | 68  | 76  | 71  | 67  | 73  | 69  | 65  | 63  |  |  |   |
| 4   | 85  | 74  | 66  | 60  | 83  | 73  | 65  | 59  | 70  | 64  | 58  | 68  | 62  | 58  | 66  | 61  | 57  | 55  |  |  |   |
| 5   | 79  | 66  | 58  | 52  | 77  | 65  | 57  | 51  | 63  | 56  | 51  | 61  | 55  | 50  | 60  | 54  | 50  | 48  |  |  |   |
| 6   | 73  | 60  | 52  | 45  | 71  | 59  | 51  | 45  | 57  | 50  | 45  | 56  | 49  | 44  | 54  | 49  | 44  | 42  |  |  |   |
| 7   | 68  | 55  | 46  | 40  | 66  | 54  | 46  | 40  | 52  | 45  | 40  | 51  | 44  | 40  | 50  | 44  | 39  | 37  |  |  |   |
| 8   | 63  | 50  | 42  | 36  | 61  | 49  | 41  | 36  | 48  | 41  | 36  | 47  | 40  | 36  | 46  | 40  | 35  | 33  |  |  |   |
| 9   | 59  | 46  | 38  | 33  | 57  | 45  | 38  | 32  | 44  | 37  | 32  | 43  | 37  | 32  | 42  | 36  | 32  | 30  |  |  |   |
| 10  | 55  | 42  | 35  | 30  | 54  | 42  | 34  | 30  | 41  | 34  | 29  | 40  | 34  | 29  | 39  | 33  | 29  | 27  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211152

CATALOG NUMBER: LE\_4B15D010 EC4B10209727 4LBCS1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 50.0   | 3.9       |
| 10°-20°   | 142.4  | 11.0      |
| 20°-30°   | 214.2  | 16.6      |
| 30°-40°   | 253.8  | 19.6      |
| 40°-50°   | 252.6  | 19.5      |
| 50°-60°   | 203.6  | 15.8      |
| 60°-70°   | 123.2  | 9.5       |
| 70°-80°   | 45.7   | 3.5       |
| 80°-90°   | 6.8    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 406.5  | 31.5      |
| 0°-40°    | 660.4  | 51.1      |
| 0°-60°    | 1116.6 | 86.4      |
| 0°-90°    | 1292.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1292.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 528 |      |
| 5°  | 526 | 50   |
| 15° | 504 | 142  |
| 25° | 465 | 214  |
| 35° | 406 | 254  |
| 45° | 329 | 253  |
| 55° | 227 | 204  |
| 65° | 124 | 123  |
| 75° | 42  | 46   |
| 85° | 6   | 7    |
| 90° | 0   |      |



TEST NUMBER: P211152

CATALOG NUMBER: LE\_4B15D010 EC4B10209727 4LBCS1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 527.8 |
| 2.5°  | 527.8 |
| 5°    | 525.5 |
| 7.5°  | 523.9 |
| 10°   | 519.2 |
| 12.5° | 511.3 |
| 15°   | 504.4 |
| 17.5° | 496.5 |
| 20°   | 487.1 |
| 22.5° | 477.7 |
| 25°   | 465.2 |
| 27.5° | 451.8 |
| 30°   | 437.0 |
| 32.5° | 422.9 |
| 35°   | 406.5 |
| 37.5° | 389.2 |
| 40°   | 368.9 |
| 42.5° | 349.3 |
| 45°   | 328.9 |
| 47.5° | 306.2 |
| 50°   | 281.2 |
| 52.5° | 255.3 |
| 55°   | 227.1 |
| 57.5° | 202.1 |
| 60°   | 173.9 |
| 62.5° | 148.8 |
| 65°   | 123.8 |
| 67.5° | 100.2 |
| 70°   | 78.3  |
| 72.5° | 58.7  |
| 75°   | 41.5  |
| 77.5° | 26.7  |
| 80°   | 15.7  |
| 82.5° | 9.4   |
| 85°   | 5.5   |
| 87.5° | 2.3   |
| 90°   | 0.0   |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)