

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843294

Luminaire Tested: **LD4C10DE010B2750 EU4C10B27 4LBWH**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P843294  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C10DE010B2750 EU4C10B27 4LBWH  
Description: 4in Downlight with BioUp LEDs  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 969.8 lumens  
Efficiency: N/A  
Efficacy: 72.9 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843294

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B27 4LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P843294

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B27 4LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	76808
5°	77101
10°	77332
15°	77330
20°	76913
25°	75110
30°	70206
35°	60785
40°	47487
45°	34071
50°	22132
55°	13258
60°	7740
65°	4971
70°	3305
75°	2516
80°	1839
85°	0



TEST NUMBER: P843294

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B27 4LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.5	6.1
10°-20°	171.5	17.7
20°-30°	253.1	26.1
30°-40°	249.8	25.8
40°-50°	152.8	15.8
50°-60°	58.6	6.0
60°-70°	18.3	1.9
70°-80°	5.4	0.6
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	484.2	49.9
0°-40°	734.0	75.7
0°-60°	945.4	97.5
0°-90°	969.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	969.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	625	
5°	625	60
15°	608	172
25°	554	253
35°	405	250
45°	196	153
55°	62	59
65°	17	18
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P843294

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B27 4LBWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	625.2
2.5°	626.4
5°	625.2
7.5°	623.8
10°	619.9
12.5°	614.6
15°	608.0
17.5°	600.1
20°	588.3
22.5°	575.1
25°	554.1
27.5°	527.7
30°	494.9
32.5°	454.0
35°	405.3
37.5°	351.3
40°	296.1
42.5°	244.7
45°	196.1
47.5°	152.6
50°	115.8
52.5°	85.6
55°	61.9
57.5°	43.4
60°	31.5
62.5°	23.7
65°	17.1
67.5°	13.2
70°	9.2
72.5°	6.6
75°	5.3
77.5°	2.6
80°	2.6
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)