

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843297

Luminaire Tested: **LD4C10DE010B2750 EU4C10B30 4LBCSMMS**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843297
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10DE010B2750 EU4C10B30 4LBCSMMS
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 808.0 lumens
Efficiency: N/A
Efficacy: 60.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843297

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P843297

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBSCMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40542
5°	40524
10°	40506
15°	40115
20°	39823
25°	39419
30°	38756
35°	38109
40°	36998
45°	35739
50°	33600
55°	30393
60°	26708
65°	22471
70°	17601
75°	12294
80°	6933
85°	4793



TEST NUMBER: P843297

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBCSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.3	3.9
10°-20°	89.0	11.0
20°-30°	133.9	16.6
30°-40°	158.7	19.6
40°-50°	157.9	19.5
50°-60°	127.3	15.8
60°-70°	77.0	9.5
70°-80°	28.6	3.5
80°-90°	4.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.2	31.5
0°-40°	412.9	51.1
0°-60°	698.2	86.4
0°-90°	808.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	808.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	330	
5°	329	31
15°	315	89
25°	291	134
35°	254	159
45°	206	158
55°	142	127
65°	77	77
75°	26	29
85°	3	4
90°	0	



TEST NUMBER: P843297

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBCSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	330.0
2.5°	330.0
5°	328.6
7.5°	327.5
10°	324.7
12.5°	319.7
15°	315.4
17.5°	310.5
20°	304.6
22.5°	298.7
25°	290.8
27.5°	282.5
30°	273.2
32.5°	264.4
35°	254.1
37.5°	243.4
40°	230.7
42.5°	218.4
45°	205.7
47.5°	191.4
50°	175.8
52.5°	159.6
55°	141.9
57.5°	126.4
60°	108.7
62.5°	93.1
65°	77.3
67.5°	62.6
70°	49.0
72.5°	36.7
75°	25.9
77.5°	16.7
80°	9.8
82.5°	5.9
85°	3.4
87.5°	1.5
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)