

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843308

Luminaire Tested: **LD4C10DE010B2750 EU4C10B30 4LBWH**

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P843308  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C10DE010B2750 EU4C10B30 4LBWH  
Description: 4in Downlight with BioUp LEDs  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 956.2 lumens  
Efficiency: N/A  
Efficacy: 71.9 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843308

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P843308

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	75715
5°	76004
10°	76234
15°	76236
20°	75815
25°	74039
30°	69199
35°	59931
40°	46813
45°	33584
50°	21807
55°	13065
60°	7641
65°	4913
70°	3269
75°	2468
80°	1839
85°	0



TEST NUMBER: P843308

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.7	6.1
10°-20°	169.1	17.7
20°-30°	249.5	26.1
30°-40°	246.3	25.8
40°-50°	150.7	15.8
50°-60°	57.8	6.0
60°-70°	18.1	1.9
70°-80°	5.3	0.6
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	477.3	49.9
0°-40°	723.6	75.7
0°-60°	932.1	97.5
0°-90°	956.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	956.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	616	
5°	616	59
15°	599	169
25°	546	250
35°	400	246
45°	193	151
55°	61	58
65°	17	18
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P843308

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	616.3
2.5°	617.6
5°	616.3
7.5°	615.0
10°	611.1
12.5°	605.9
15°	599.4
17.5°	591.6
20°	579.9
22.5°	567.0
25°	546.2
27.5°	520.3
30°	487.8
32.5°	447.6
35°	399.6
37.5°	346.4
40°	291.9
42.5°	241.4
45°	193.3
47.5°	150.5
50°	114.1
52.5°	84.4
55°	61.0
57.5°	42.8
60°	31.1
62.5°	23.4
65°	16.9
67.5°	13.0
70°	9.1
72.5°	6.5
75°	5.2
77.5°	2.6
80°	2.6
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)