

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430510

Luminaire Tested: **LAM4B312R509024DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430510
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B312R509024DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 50 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3359.0 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.74
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430510

CATALOG NUMBER: LAM4B312R509024DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P430510

CATALOG NUMBER: LAM4B312R509024DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																											
2	110	105	102	99	107	104	100	98	100	98	96	97	95	93	95	93	92	90																											
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85																											
4	101	94	89	86	99	93	89	85	91	87	84	89	86	83	87	84	82	81																											
5	96	89	84	80	95	88	84	80	87	83	79	85	81	79	84	80	78	77																											
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73																											
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69																											
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66																											
9	82	73	68	65	81	73	68	65	72	68	64	71	67	64	70	67	64	63																											
10	79	70	65	62	78	70	65	62	69	64	61	68	64	61	68	64	61	60																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	887763
5°	844595
10°	819778
15°	786567
20°	647112
25°	518486
30°	270483
35°	87224
40°	14827
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P430510

CATALOG NUMBER: LAM4B312R509024DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	491.8	14.6
10°-20°	1276.3	38.0
20°-30°	1241.6	37.0
30°-40°	341.8	10.2
40°-50°	7.5	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3009.7	89.6
0°-40°	3351.5	99.8
0°-60°	3359.0	100.0
0°-90°	3359.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3359.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5510	
5°	5223	492
15°	4716	1276
25°	2917	1242
35°	444	342
45°	0	7
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P430510

CATALOG NUMBER: LAM4B312R509024DE01021MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	5510.5
2.5°	5412.1
5°	5222.6
7.5°	5069.9
10°	5011.2
12.5°	5006.8
15°	4716.0
17.5°	4179.9
20°	3774.5
22.5°	3438.2
25°	2916.8
27.5°	2053.2
30°	1454.0
32.5°	879.7
35°	443.5
37.5°	198.3
40°	70.5
42.5°	5.9
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)