

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843318

Luminaire Tested: **LD4C10DE010B2750 EU4C10B35 4LBNH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843318
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10DE010B2750 EU4C10B35 4LBNH
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 733.0 lumens
Efficiency: N/A
Efficacy: 55.1 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843318

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B35 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P843318

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B35 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	76	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113050
5°	110534
10°	102194
15°	91715
20°	80718
25°	69471
30°	55949
35°	37239
40°	19373
45°	8757
50°	3803
55°	2570
60°	1646
65°	1163
70°	934
75°	665
80°	0
85°	0



TEST NUMBER: P843318

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B35 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.0	11.3
10°-20°	201.4	27.5
20°-30°	233.8	31.9
30°-40°	154.8	21.1
40°-50°	43.4	5.9
50°-60°	10.9	1.5
60°-70°	4.1	0.6
70°-80°	1.4	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	518.2	70.7
0°-40°	673.1	91.8
0°-60°	727.4	99.2
0°-90°	733.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	733.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	920	
5°	896	83
15°	721	201
25°	512	234
35°	248	155
45°	50	43
55°	12	11
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P843318

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B35 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	920.2
2.5°	916.2
5°	896.3
7.5°	861.8
10°	819.2
12.5°	771.4
15°	721.1
17.5°	671.9
20°	617.4
22.5°	567.0
25°	512.5
27.5°	460.8
30°	394.4
32.5°	324.0
35°	248.3
37.5°	177.9
40°	120.8
42.5°	78.4
45°	50.4
47.5°	30.6
50°	19.9
52.5°	14.6
55°	12.0
57.5°	9.3
60°	6.7
62.5°	5.3
65°	4.0
67.5°	2.6
70°	2.6
72.5°	1.4
75°	1.4
77.5°	1.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)