

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843319

Luminaire Tested: **LD4C10DE010B2750 EU4C10B35 4LBNLI**

Issue Date: 2/16/2023

Test Information

Test Method: LM-79-08
Report Number: P843319
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 2/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10DE010B2750 EU4C10B35 4LBNLI
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 864.1 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843319

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B35 4LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P843319

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B35 4LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	273189
5°	245832
10°	190566
15°	137935
20°	95504
25°	69634
30°	50587
35°	29935
40°	12589
45°	3927
50°	497
55°	300
60°	344
65°	407
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P843319

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B35 4LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.2	20.3
10°-20°	300.0	34.7
20°-30°	238.4	27.6
30°-40°	126.2	14.6
40°-50°	21.7	2.5
50°-60°	1.6	0.2
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	713.7	82.6
0°-40°	839.9	97.2
0°-60°	863.3	99.9
0°-90°	864.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	864.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2224	
5°	1993	175
15°	1084	300
25°	514	238
35°	200	126
45°	23	22
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P843319

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B35 4LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2223.7
2.5°	2166.5
5°	1993.4
7.5°	1767.2
10°	1527.6
12.5°	1296.1
15°	1084.5
17.5°	887.6
20°	730.5
22.5°	610.8
25°	513.7
27.5°	435.1
30°	356.6
32.5°	276.8
35°	199.6
37.5°	131.8
40°	78.5
42.5°	45.3
45°	22.6
47.5°	8.0
50°	2.6
52.5°	2.6
55°	1.4
57.5°	1.4
60°	1.4
62.5°	1.4
65°	1.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)