

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430538

Luminaire Tested: **LAM4B312R559027DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430538
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-898-142)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B312R559027DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 55 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3386.1 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.81
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430538

CATALOG NUMBER: LAM4B312R559027DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P430538

CATALOG NUMBER: LAM4B312R559027DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	95																			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90																			
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85																			
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80																			
5	96	89	83	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76																			
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72																			
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	68																			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	72	69	66	65																			
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62																			
10	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	63	60	59																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2278920
5°	2310853
10°	2364927
15°	2266043
20°	2058853
25°	1654547
30°	952434
35°	276398
40°	42250
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P430538

CATALOG NUMBER: LAM4B312R559027DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	447.4	13.2
10°-20°	1234.3	36.5
20°-30°	1332.3	39.3
30°-40°	364.4	10.8
40°-50°	7.7	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3014.0	89.0
0°-40°	3378.4	99.8
0°-60°	3386.1	100.0
0°-90°	3386.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3386.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4619	
5°	4666	447
15°	4436	1234
25°	3039	1332
35°	459	364
45°	0	8
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P430538

CATALOG NUMBER: LAM4B312R559027DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	4619.0
2.5°	4600.3
5°	4665.9
7.5°	4717.4
10°	4720.5
12.5°	4600.3
15°	4436.4
17.5°	4219.4
20°	3921.3
22.5°	3537.3
25°	3039.3
27.5°	2404.0
30°	1671.8
32.5°	916.3
35°	458.9
37.5°	196.7
40°	65.6
42.5°	9.4
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)