

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843324

Luminaire Tested: **LD4C10DE010B2750 EU4C10B40 4LBCSMB**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843324
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10DE010B2750 EU4C10B40 4LBCSMB
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 803.8 lumens
Efficiency: N/A
Efficacy: 60.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843324

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B40 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P843324

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B40 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40333
5°	40302
10°	40294
15°	39899
20°	39614
25°	39229
30°	38557
35°	37914
40°	36790
45°	35565
50°	33428
55°	30243
60°	26585
65°	22384
70°	17493
75°	12246
80°	6863
85°	4793



TEST NUMBER: P843324

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B40 4LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.1	3.9
10°-20°	88.6	11.0
20°-30°	133.2	16.6
30°-40°	157.9	19.6
40°-50°	157.1	19.5
50°-60°	126.7	15.8
60°-70°	76.6	9.5
70°-80°	28.4	3.5
80°-90°	4.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	252.9	31.5
0°-40°	410.8	51.1
0°-60°	694.5	86.4
0°-90°	803.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	803.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	328	
5°	327	31
15°	314	89
25°	289	133
35°	253	158
45°	205	157
55°	141	127
65°	77	77
75°	26	28
85°	3	4
90°	0	



TEST NUMBER: P843324

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B40 4LBCSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	328.3
2.5°	328.3
5°	326.8
7.5°	325.9
10°	323.0
12.5°	318.0
15°	313.7
17.5°	308.8
20°	303.0
22.5°	297.2
25°	289.4
27.5°	281.0
30°	271.8
32.5°	263.0
35°	252.8
37.5°	242.1
40°	229.4
42.5°	217.2
45°	204.7
47.5°	190.4
50°	174.9
52.5°	158.8
55°	141.2
57.5°	125.8
60°	108.2
62.5°	92.5
65°	77.0
67.5°	62.3
70°	48.7
72.5°	36.5
75°	25.8
77.5°	16.6
80°	9.7
82.5°	5.8
85°	3.4
87.5°	1.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)