

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431714

Luminaire Tested: **LAMR4B312R609027DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431714
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B312R609027DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3188.5 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431714

CATALOG NUMBER: LAMR4B312R609027DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P431714

CATALOG NUMBER: LAMR4B312R609027DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82		
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77		
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	69	67		
7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63		
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	60	59		
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1808039
5°	1747441
10°	1731173
15°	1688193
20°	1557962
25°	1395202
30°	1079649
35°	646755
40°	248479
45°	90846
50°	3531
55°	2667
60°	3059
65°	1751
70°	2164
75°	2859
80°	4262
85°	0



TEST NUMBER: P431714

CATALOG NUMBER: LAMR4B312R609027DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	335.0	10.5
10°-20°	919.5	28.8
20°-30°	1147.1	36.0
30°-40°	668.2	21.0
40°-50°	111.5	3.5
50°-60°	2.9	0.1
60°-70°	2.1	0.1
70°-80°	1.6	0.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2401.5	75.3
0°-40°	3069.8	96.3
0°-60°	3184.2	99.9
0°-90°	3188.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3188.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3665	
5°	3528	335
15°	3305	919
25°	2563	1147
35°	1074	668
45°	130	112
55°	3	3
65°	2	2
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P431714

CATALOG NUMBER: LAMR4B312R609027DE01021MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3664.6
2.5°	3604.2
5°	3528.3
7.5°	3484.9
10°	3455.5
12.5°	3407.4
15°	3305.1
17.5°	3151.7
20°	2967.3
22.5°	2779.9
25°	2562.9
27.5°	2262.3
30°	1895.1
32.5°	1484.4
35°	1073.8
37.5°	677.1
40°	385.8
42.5°	226.2
45°	130.2
47.5°	44.9
50°	4.6
52.5°	3.1
55°	3.1
57.5°	3.1
60°	3.1
62.5°	3.1
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)