

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843360

Luminaire Tested: **LD4C15DE010B2750 EU4C15B27 4LBNH**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P843360
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15DE010B2750 EU4C15B27 4LBNH
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 938.1 lumens
Efficiency: N/A
Efficacy: 55.2 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843360

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B27 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P843360

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B27 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	144709
5°	141476
10°	130811
15°	117381
20°	103335
25°	88937
30°	71610
35°	47663
40°	24794
45°	11224
50°	4874
55°	3256
60°	2113
65°	1483
70°	1221
75°	807
80°	0
85°	0



TEST NUMBER: P843360

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B27 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.3	11.3
10°-20°	257.8	27.5
20°-30°	299.3	31.9
30°-40°	198.2	21.1
40°-50°	55.6	5.9
50°-60°	14.0	1.5
60°-70°	5.2	0.6
70°-80°	1.8	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	663.3	70.7
0°-40°	861.5	91.8
0°-60°	931.1	99.2
0°-90°	938.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	938.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1178	
5°	1147	106
15°	923	258
25°	656	299
35°	318	198
45°	65	56
55°	15	14
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P843360

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B27 4LBNH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1177.9
2.5°	1172.7
5°	1147.2
7.5°	1103.0
10°	1048.6
12.5°	987.4
15°	922.9
17.5°	860.0
20°	790.4
22.5°	725.7
25°	656.1
27.5°	589.7
30°	504.8
32.5°	414.7
35°	317.8
37.5°	227.7
40°	154.6
42.5°	100.3
45°	64.6
47.5°	39.1
50°	25.5
52.5°	18.7
55°	15.2
57.5°	12.0
60°	8.6
62.5°	6.8
65°	5.1
67.5°	3.4
70°	3.4
72.5°	1.7
75°	1.7
77.5°	1.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)