

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431622

Luminaire Tested: **LAMR4B312R409030DE01021MW**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P431622  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-7)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B312R409030DE01021MW  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 40 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3803.6 lumens  
Efficiency: N/A  
Efficacy: 93.0 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6  
Luminous Opening: Circular (Dia: 0.29' x H: 0')  
CIE Type: Direct

Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P431622  
CATALOG NUMBER: LAMR4B312R409030DE01021MW

### Luminous Intensity Polar Plot





TEST NUMBER: P431622

CATALOG NUMBER: LAMR4B312R409030DE01021MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																											
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																											
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																											
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	86																											
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82																											
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																											
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77																											
8	91	83	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	74																											
9	88	81	76	73	87	80	76	73	79	75	73	79	75	73	78	75	72	71																											
10	85	78	73	71	84	77	73	70	77	73	70	76	73	70	75	72	70	69																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1433921
5°	1441225
10°	1430996
15°	1290981
20°	814509
25°	293337
30°	61463
35°	18703
40°	3722
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P431622

CATALOG NUMBER: LAMR4B312R409030DE01021MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	845.1	22.2
10°-20°	2020.7	53.1
20°-30°	861.6	22.7
30°-40°	73.9	1.9
40°-50°	2.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3727.5	98.0
0°-40°	3801.4	99.9
0°-60°	3803.6	100.0
0°-90°	3803.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3803.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8901	
5°	8912	845
15°	7740	2021
25°	1650	862
35°	95	74
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P431622

CATALOG NUMBER: LAMR4B312R409030DE01021MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8900.6
2.5°	8892.5
5°	8911.9
7.5°	8858.7
10°	8747.5
12.5°	8415.5
15°	7740.3
17.5°	6422.0
20°	4750.9
22.5°	3128.0
25°	1650.2
27.5°	668.8
30°	330.4
32.5°	175.7
35°	95.1
37.5°	48.3
40°	17.7
42.5°	3.2
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)