

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843380

Luminaire Tested: **LD4C15DE010B2750 EU4C15B35 4LBCSMB**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843380
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15DE010B2750 EU4C15B35 4LBCSMB
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1049.1 lumens
Efficiency: N/A
Efficacy: 61.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843380

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P843380

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52630
5°	52609
10°	52594
15°	52083
20°	51694
25°	51199
30°	50317
35°	49492
40°	48016
45°	46406
50°	43634
55°	39475
60°	34694
65°	29215
70°	22845
75°	15949
80°	8985
85°	6202



TEST NUMBER: P843380

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.6	3.9
10°-20°	115.6	11.0
20°-30°	173.9	16.6
30°-40°	206.1	19.6
40°-50°	205.1	19.5
50°-60°	165.3	15.8
60°-70°	100.0	9.5
70°-80°	37.1	3.5
80°-90°	5.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	330.1	31.5
0°-40°	536.1	51.1
0°-60°	906.5	86.4
0°-90°	1049.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1049.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	428	
5°	427	41
15°	410	116
25°	378	174
35°	330	206
45°	267	205
55°	184	165
65°	100	100
75°	34	37
85°	4	6
90°	0	



TEST NUMBER: P843380

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBCSMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	428.4
2.5°	428.4
5°	426.6
7.5°	425.4
10°	421.6
12.5°	415.1
15°	409.5
17.5°	403.2
20°	395.4
22.5°	387.8
25°	377.7
27.5°	366.8
30°	354.7
32.5°	343.3
35°	330.0
37.5°	316.0
40°	299.4
42.5°	283.6
45°	267.1
47.5°	248.5
50°	228.3
52.5°	207.2
55°	184.3
57.5°	164.0
60°	141.2
62.5°	120.8
65°	100.5
67.5°	81.3
70°	63.6
72.5°	47.7
75°	33.6
77.5°	21.7
80°	12.7
82.5°	7.6
85°	4.4
87.5°	1.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)