

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843386

Luminaire Tested: **LD4C15DE010B2750 EU4C15B35 4LBMH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15DE010B2750 EU4C15B35 4LBMH
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1142.3 lumens
Efficiency: N/A
Efficacy: 67.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843386

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P843386

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	139144
5°	137123
10°	131398
15°	124109
20°	115847
25°	105163
30°	87797
35°	63605
40°	39805
45°	22760
50°	11869
55°	6661
60°	4226
65°	2529
70°	1868
75°	807
80°	1203
85°	0



TEST NUMBER: P843386

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.2	9.1
10°-20°	273.4	23.9
20°-30°	351.4	30.8
30°-40°	264.4	23.1
40°-50°	106.2	9.3
50°-60°	30.2	2.6
60°-70°	9.6	0.8
70°-80°	2.7	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	729.0	63.8
0°-40°	993.4	87.0
0°-60°	1129.8	98.9
0°-90°	1142.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1142.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1133	
5°	1112	104
15°	976	273
25°	776	351
35°	424	264
45°	131	106
55°	31	30
65°	9	10
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P843386

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1132.6
2.5°	1125.7
5°	1111.9
7.5°	1086.1
10°	1053.3
12.5°	1013.6
15°	975.8
17.5°	932.6
20°	886.1
22.5°	836.2
25°	775.8
27.5°	703.3
30°	618.9
32.5°	524.1
35°	424.1
37.5°	330.9
40°	248.2
42.5°	182.8
45°	131.0
47.5°	89.7
50°	62.1
52.5°	43.2
55°	31.1
57.5°	22.4
60°	17.2
62.5°	12.1
65°	8.7
67.5°	6.9
70°	5.2
72.5°	3.5
75°	1.7
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)