

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431647

Luminaire Tested: **LAMR4B312R459035DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-908-8)
Test Lab: INNOVATION CENTER (G2)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B312R459035DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 45 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3829.2 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.66
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431647

CATALOG NUMBER: LAMR4B312R459035DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P431647

CATALOG NUMBER: LAMR4B312R459035DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95																			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89																			
3	105	99	94	91	103	98	93	90	95	92	89	93	90	87	90	88	86	85																			
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80																			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76																			
6	92	85	79	76	91	84	79	75	82	78	75	81	77	74	80	77	74	73																			
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69																			
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66																			
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	65	63																			
10	79	71	66	62	78	70	66	62	70	65	62	69	65	62	68	65	62	61																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3538518
5°	3537276
10°	3362249
15°	2953456
20°	2259367
25°	1318988
30°	539853
35°	228274
40°	124433
45°	80380
50°	62787
55°	54363
60°	44009
65°	34673
70°	32169
75°	28403
80°	31538
85°	20945



TEST NUMBER: P431647

CATALOG NUMBER: LAMR4B312R459035DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	668.3	17.5
10°-20°	1574.2	41.1
20°-30°	1109.2	29.0
30°-40°	273.0	7.1
40°-50°	95.2	2.5
50°-60°	56.4	1.5
60°-70°	31.2	0.8
70°-80°	17.2	0.4
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3351.7	87.5
0°-40°	3624.7	94.7
0°-60°	3776.3	98.6
0°-90°	3829.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3829.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7172	
5°	7142	668
15°	5782	1574
25°	2423	1109
35°	379	273
45°	115	95
55°	63	56
65°	30	31
75°	15	17
85°	4	5
90°	0	



TEST NUMBER: P431647

CATALOG NUMBER: LAMR4B312R459035DE01021MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	7172.0
2.5°	7153.4
5°	7142.2
7.5°	7012.2
10°	6711.2
12.5°	6302.4
15°	5782.2
17.5°	5109.6
20°	4303.2
22.5°	3377.9
25°	2422.9
27.5°	1564.5
30°	947.6
32.5°	576.0
35°	379.0
37.5°	267.6
40°	193.2
42.5°	148.6
45°	115.2
47.5°	96.6
50°	81.8
52.5°	70.6
55°	63.2
57.5°	55.7
60°	44.6
62.5°	37.2
65°	29.7
67.5°	26.0
70°	22.3
72.5°	18.6
75°	14.9
77.5°	14.9
80°	11.1
82.5°	7.4
85°	3.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)