

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843400

Luminaire Tested: **LD4C15DE010B2750 EU4C15B40 4LBMH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843400
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15DE010B2750 EU4C15B40 4LBMH
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1131.7 lumens
Efficiency: N/A
Efficacy: 66.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843400

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B40 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P843400

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B40 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79				79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73				73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67				67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62				62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	137854
5°	135852
10°	130188
15°	122952
20°	114762
25°	104187
30°	86988
35°	63020
40°	39452
45°	22552
50°	11773
55°	6597
60°	4202
65°	2500
70°	1832
75°	807
80°	1203
85°	0



TEST NUMBER: P843400

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B40 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.3	9.1
10°-20°	270.9	23.9
20°-30°	348.1	30.8
30°-40°	261.9	23.1
40°-50°	105.2	9.3
50°-60°	29.9	2.6
60°-70°	9.5	0.8
70°-80°	2.7	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	722.2	63.8
0°-40°	984.2	87.0
0°-60°	1119.3	98.9
0°-90°	1131.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1131.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1122	
5°	1102	103
15°	967	271
25°	769	348
35°	420	262
45°	130	105
55°	31	30
65°	9	10
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P843400

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B40 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1122.1
2.5°	1115.3
5°	1101.6
7.5°	1076.0
10°	1043.6
12.5°	1004.3
15°	966.7
17.5°	923.9
20°	877.8
22.5°	828.3
25°	768.6
27.5°	696.8
30°	613.2
32.5°	519.2
35°	420.2
37.5°	327.9
40°	246.0
42.5°	181.1
45°	129.8
47.5°	88.8
50°	61.6
52.5°	42.7
55°	30.8
57.5°	22.2
60°	17.1
62.5°	12.0
65°	8.6
67.5°	6.9
70°	5.1
72.5°	3.4
75°	1.7
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)