

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430580

Luminaire Tested: **LAM4B312R609730DE01021MMS**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P430580  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAM4B312R609730DE01021MMS  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3198.0 lumens  
Efficiency: N/A  
Efficacy: 78.2 lumens/watt  
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P430580

CATALOG NUMBER: LAM4B312R609730DE01021MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P430580

CATALOG NUMBER: LAM4B312R609730DE01021MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82			82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77			77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72			72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	69	67			67
7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63			63
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	60	59			59
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56			56
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1813269
5°	1752492
10°	1736133
15°	1693096
20°	1562477
25°	1399230
30°	1082783
35°	648622
40°	249187
45°	91056
50°	3608
55°	2667
60°	3059
65°	1868
70°	2308
75°	3050
80°	4546
85°	0



TEST NUMBER: P430580

CATALOG NUMBER: LAM4B312R609730DE01021MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	336.0	10.5
10°-20°	922.1	28.8
20°-30°	1150.4	36.0
30°-40°	670.2	21.0
40°-50°	111.9	3.5
50°-60°	3.0	0.1
60°-70°	2.1	0.1
70°-80°	1.7	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2408.5	75.3
0°-40°	3078.7	96.3
0°-60°	3193.5	99.9
0°-90°	3198.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3198.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3675	
5°	3538	336
15°	3315	922
25°	2570	1150
35°	1077	670
45°	130	112
55°	3	3
65°	2	2
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P430580

CATALOG NUMBER: LAM4B312R609730DE01021MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3675.2
2.5°	3614.6
5°	3538.5
7.5°	3495.0
10°	3465.4
12.5°	3417.3
15°	3314.7
17.5°	3160.9
20°	2975.9
22.5°	2787.9
25°	2570.3
27.5°	2268.9
30°	1900.6
32.5°	1488.7
35°	1076.9
37.5°	679.1
40°	386.9
42.5°	226.9
45°	130.5
47.5°	45.1
50°	4.7
52.5°	3.1
55°	3.1
57.5°	3.1
60°	3.1
62.5°	3.1
65°	1.6
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)