

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843424

Luminaire Tested: **LD4C20DE010B2750 EU4C20B27 4LBCSMW**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843424
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C20DE010B2750 EU4C20B27 4LBSCMW
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1638.3 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843424

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B27 4LBCSMW

Luminous Intensity Polar Plot





TEST NUMBER: P843424

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B27 4LBSCMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82201
5°	82158
10°	82122
15°	81324
20°	80744
25°	79936
30°	78590
35°	77283
40°	74991
45°	72450
50°	68117
55°	61665
60°	54154
65°	45581
70°	35633
75°	24968
80°	14079
85°	9726



TEST NUMBER: P843424

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B27 4LBCSMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.4	3.9
10°-20°	180.5	11.0
20°-30°	271.5	16.6
30°-40°	321.8	19.6
40°-50°	320.2	19.5
50°-60°	258.1	15.8
60°-70°	156.1	9.5
70°-80°	58.0	3.5
80°-90°	8.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	515.4	31.5
0°-40°	837.2	51.1
0°-60°	1415.6	86.4
0°-90°	1638.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1638.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	669	
5°	666	63
15°	639	181
25°	590	272
35°	515	322
45°	417	320
55°	288	258
65°	157	156
75°	53	58
85°	7	9
90°	0	



TEST NUMBER: P843424

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B27 4LBCSMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	669.1
2.5°	669.1
5°	666.2
7.5°	664.2
10°	658.3
12.5°	648.3
15°	639.4
17.5°	629.5
20°	617.6
22.5°	605.6
25°	589.7
27.5°	572.8
30°	554.0
32.5°	536.1
35°	515.3
37.5°	493.4
40°	467.6
42.5°	442.8
45°	417.0
47.5°	388.2
50°	356.4
52.5°	323.6
55°	287.9
57.5°	256.2
60°	220.4
62.5°	188.7
65°	156.8
67.5°	127.0
70°	99.2
72.5°	74.5
75°	52.6
77.5°	33.7
80°	19.9
82.5°	12.0
85°	6.9
87.5°	2.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)