

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843465

Luminaire Tested: **LD4C20DE010B2750 EU4C20B40 4LBCSMMS**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843465
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C20DE010B2750 EU4C20B40 4LBSCMMS
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1344.3 lumens
Efficiency: N/A
Efficacy: 61.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843465

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B40 4LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P843465

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B40 4LBCSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67447
5°	67408
10°	67377
15°	66735
20°	66245
25°	65594
30°	64489
35°	63410
40°	61535
45°	59437
50°	55904
55°	50591
60°	44448
65°	37413
70°	29239
75°	20506
80°	11532
85°	7894



TEST NUMBER: P843465

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B40 4LBCSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.0	3.9
10°-20°	148.1	11.0
20°-30°	222.8	16.6
30°-40°	264.0	19.6
40°-50°	262.8	19.5
50°-60°	211.9	15.8
60°-70°	128.1	9.5
70°-80°	47.6	3.5
80°-90°	7.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.9	31.5
0°-40°	687.0	51.1
0°-60°	1161.6	86.4
0°-90°	1344.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1344.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	549	
5°	547	52
15°	525	148
25°	484	223
35°	423	264
45°	342	263
55°	236	212
65°	129	128
75°	43	48
85°	6	7
90°	0	



TEST NUMBER: P843465

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B40 4LBCSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	549.0
2.5°	549.0
5°	546.6
7.5°	545.0
10°	540.1
12.5°	532.0
15°	524.7
17.5°	516.5
20°	506.7
22.5°	497.0
25°	483.9
27.5°	470.0
30°	454.6
32.5°	439.9
35°	422.8
37.5°	404.9
40°	383.7
42.5°	363.4
45°	342.1
47.5°	318.5
50°	292.5
52.5°	265.6
55°	236.2
57.5°	210.3
60°	180.9
62.5°	154.7
65°	128.7
67.5°	104.3
70°	81.4
72.5°	61.1
75°	43.2
77.5°	27.7
80°	16.3
82.5°	9.8
85°	5.6
87.5°	2.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)