

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843466

Luminaire Tested: **LD4C20DE010B2750 EU4C20B40 4LBCSMW**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843466
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C20DE010B2750 EU4C20B40 4LBSCMW
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1643.6 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843466

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B40 4LBCSMW

Luminous Intensity Polar Plot





TEST NUMBER: P843466

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B40 4LBSCMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82472
5°	82417
10°	82384
15°	81591
20°	81005
25°	80194
30°	78845
35°	77538
40°	75247
45°	72693
50°	68347
55°	61836
60°	54350
65°	45756
70°	35740
75°	25063
80°	14079
85°	9726



TEST NUMBER: P843466

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B40 4LBCSMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.6	3.9
10°-20°	181.1	11.0
20°-30°	272.4	16.6
30°-40°	322.8	19.6
40°-50°	321.3	19.5
50°-60°	259.0	15.8
60°-70°	156.6	9.5
70°-80°	58.1	3.5
80°-90°	8.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	517.1	31.5
0°-40°	839.9	51.1
0°-60°	1420.2	86.4
0°-90°	1643.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1643.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	671	
5°	668	64
15°	642	181
25°	592	272
35°	517	323
45°	418	321
55°	289	259
65°	157	157
75°	53	58
85°	7	9
90°	0	



TEST NUMBER: P843466

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B40 4LBCSMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	671.3
2.5°	671.3
5°	668.3
7.5°	666.3
10°	660.4
12.5°	650.3
15°	641.5
17.5°	631.5
20°	619.6
22.5°	607.6
25°	591.6
27.5°	574.6
30°	555.8
32.5°	537.8
35°	517.0
37.5°	495.1
40°	469.2
42.5°	444.3
45°	418.4
47.5°	389.4
50°	357.6
52.5°	324.7
55°	288.7
57.5°	257.0
60°	221.2
62.5°	189.2
65°	157.4
67.5°	127.4
70°	99.5
72.5°	74.7
75°	52.8
77.5°	33.8
80°	19.9
82.5°	12.0
85°	6.9
87.5°	3.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)