

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432047

Luminaire Tested: **LAMR4B412R709024DE01021MMS**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P432047  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B412R709024DE01021MMS  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4726.5 lumens  
Efficiency: N/A  
Efficacy: 87.4 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 54.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P432047

CATALOG NUMBER: LAMR4B412R709024DE01021MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P432047

CATALOG NUMBER: LAMR4B412R709024DE01021MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	64	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50	50	50	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46	46
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	48	44	43	43	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1714050
5°	1682165
10°	1701615
15°	1749742
20°	1752753
25°	1590146
30°	1420846
35°	1247916
40°	918753
45°	514586
50°	253219
55°	141930
60°	86144
65°	56621
70°	41978
75°	36982
80°	27560
85°	27738



TEST NUMBER: P432047

CATALOG NUMBER: LAMR4B412R709024DE01021MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	324.7	6.9
10°-20°	965.3	20.4
20°-30°	1339.6	28.3
30°-40°	1260.3	26.7
40°-50°	601.6	12.7
50°-60°	159.1	3.4
60°-70°	50.2	1.1
70°-80°	20.5	0.4
80°-90°	5.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2629.5	55.6
0°-40°	3889.8	82.3
0°-60°	4650.5	98.4
0°-90°	4726.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4726.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3474	
5°	3396	325
15°	3426	965
25°	2921	1340
35°	2072	1260
45°	738	602
55°	165	159
65°	48	50
75°	19	20
85°	5	5
90°	0	



TEST NUMBER: P432047

CATALOG NUMBER: LAMR4B412R709024DE01021MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3474.1
2.5°	3430.5
5°	3396.5
7.5°	3391.6
10°	3396.5
12.5°	3406.2
15°	3425.6
17.5°	3425.6
20°	3338.3
22.5°	3153.9
25°	2921.0
27.5°	2688.1
30°	2494.0
32.5°	2304.8
35°	2071.9
37.5°	1771.0
40°	1426.5
42.5°	1062.6
45°	737.5
47.5°	490.1
50°	329.9
52.5°	228.1
55°	165.0
57.5°	116.5
60°	87.3
62.5°	63.1
65°	48.5
67.5°	34.0
70°	29.1
72.5°	24.3
75°	19.4
77.5°	14.6
80°	9.7
82.5°	9.7
85°	4.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)