

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P431857

Luminaire Tested: **LAMR4B412R309027DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P431857
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B412R309027DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5322.2 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 54.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P431857

CATALOG NUMBER: LAMR4B412R309027DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P431857

CATALOG NUMBER: LAMR4B412R309027DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																																
RC	80									70									50									30									10									0														
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																														
RCR																																																												
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																										
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96	96	95	94	93	92	91	90	89	88	87	85	84	81																													
2	111	107	104	102	109	106	103	100	102	100	98	96	94	92	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50																									
3	107	103	99	96	105	101	98	95	99	96	94	92	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40																						
4	104	98	94	91	102	97	94	91	95	92	90	88	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30																			
5	101	95	91	87	99	94	90	87	92	89	86	84	82	80	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20																
6	98	91	87	84	97	91	87	84	89	86	83	81	79	77	75	73	71	69	67	65	63	61	59	57	55	53	51	49	47	45	43	41	39	37	35	33	31	29	27	25	23	21	19	17	15	13	11	9	7	5	3	1								
7	95	88	84	81	94	88	84	81	87	83	81	79	77	75	73	71	69	67	65	63	61	59	57	55	53	51	49	47	45	43	41	39	37	35	33	31	29	27	25	23	21	19	17	15	13	11	9	7	5	3	1									
8	92	86	81	79	91	85	81	78	84	81	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2	0										
9	90	83	79	76	89	83	79	76	82	78	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2	0											
10	88	81	77	74	87	80	77	74	80	76	74	72	70	68	66	64	62	60	58	56	54	52	50	48	46	44	42	40	38	36	34	32	30	28	26	24	22	20	18	16	14	12	10	8	6	4	2	0												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9643251
5°	9432554
10°	8178523
15°	5069072
20°	1857867
25°	621033
30°	304849
35°	152022
40°	94291
45°	59866
50°	42600
55°	34751
60°	29899
65°	23582
70°	29139
75°	28785
80°	28697
85°	28304



TEST NUMBER: P431857

CATALOG NUMBER: LAMR4B412R309027DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1735.8	32.6
10°-20°	2620.6	49.2
20°-30°	638.9	12.0
30°-40°	175.0	3.3
40°-50°	70.4	1.3
50°-60°	37.7	0.7
60°-70°	22.5	0.4
70°-80°	17.3	0.3
80°-90°	4.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4995.3	93.9
0°-40°	5170.2	97.1
0°-60°	5278.4	99.2
0°-90°	5322.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5322.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19545	
5°	19046	###
15°	9924	2621
25°	1141	639
35°	252	175
45°	86	70
55°	40	38
65°	20	22
75°	15	17
85°	5	4
90°	0	



TEST NUMBER: P431857

CATALOG NUMBER: LAMR4B412R309027DE01021MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	19545.3
2.5°	19414.0
5°	19045.5
7.5°	18167.2
10°	16324.7
12.5°	13437.4
15°	9924.1
17.5°	6395.6
20°	3538.5
22.5°	1887.9
25°	1140.8
27.5°	772.3
30°	535.1
32.5°	363.4
35°	252.4
37.5°	186.8
40°	146.4
42.5°	111.1
45°	85.8
47.5°	70.7
50°	55.5
52.5°	50.5
55°	40.4
57.5°	35.3
60°	30.3
62.5°	25.2
65°	20.2
67.5°	20.2
70°	20.2
72.5°	20.2
75°	15.1
77.5°	15.1
80°	10.1
82.5°	5.0
85°	5.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)