

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843485

Luminaire Tested: **LD4C20DE010B2750 EU4C20B50 4LBMLI**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P843485
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C20DE010B2750 EU4C20B50 4LBMLI
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1905.9 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843485

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B50 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P843485

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B50 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	70	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	369101
5°	362828
10°	333378
15°	279189
20°	223680
25°	179717
30°	133787
35°	76443
40°	35876
45°	15237
50°	4855
55°	2463
60°	1695
65°	1366
70°	826
75°	0
80°	0
85°	0



TEST NUMBER: P843485

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B50 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	272.0	14.3
10°-20°	608.2	31.9
20°-30°	604.7	31.7
30°-40°	329.3	17.3
40°-50°	76.1	4.0
50°-60°	10.7	0.6
60°-70°	4.0	0.2
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1484.9	77.9
0°-40°	1814.2	95.2
0°-60°	1901.0	99.7
0°-90°	1905.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1905.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3004	
5°	2942	272
15°	2195	608
25°	1326	605
35°	510	329
45°	88	76
55°	12	11
65°	5	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P843485

CATALOG NUMBER: LD4C20DE010B2750 EU4C20B50 4LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3004.4
2.5°	2997.5
5°	2942.1
7.5°	2829.3
10°	2672.4
12.5°	2441.9
15°	2195.1
17.5°	1950.7
20°	1710.9
22.5°	1515.0
25°	1325.8
27.5°	1146.1
30°	943.1
32.5°	717.2
35°	509.7
37.5°	343.5
40°	223.7
42.5°	140.7
45°	87.7
47.5°	50.8
50°	25.4
52.5°	13.9
55°	11.5
57.5°	6.9
60°	6.9
62.5°	4.7
65°	4.7
67.5°	2.3
70°	2.3
72.5°	2.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)