

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843506

Luminaire Tested: **LD4C25DE010B2750 EU4C25B30 4LBCSMB**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843506
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25DE010B2750 EU4C25B30 4LBCSMB
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1695.4 lumens
Efficiency: N/A
Efficacy: 56.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843506

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B30 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P843506

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B30 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85064
5°	85019
10°	84979
15°	84173
20°	83555
25°	82728
30°	81314
35°	79982
40°	77605
45°	74969
50°	70506
55°	63785
60°	56046
65°	47180
70°	36890
75°	25869
80°	14503
85°	10008



TEST NUMBER: P843506

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B30 4LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.6	3.9
10°-20°	186.8	11.0
20°-30°	281.0	16.6
30°-40°	333.0	19.6
40°-50°	331.4	19.5
50°-60°	267.1	15.8
60°-70°	161.6	9.5
70°-80°	60.0	3.5
80°-90°	8.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	533.4	31.5
0°-40°	866.4	51.1
0°-60°	1464.9	86.4
0°-90°	1695.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1695.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	692	
5°	689	66
15°	662	187
25°	610	281
35°	533	333
45°	432	331
55°	298	267
65°	162	162
75°	54	60
85°	7	9
90°	0	



TEST NUMBER: P843506

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B30 4LBCSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	692.4
2.5°	692.4
5°	689.4
7.5°	687.4
10°	681.2
12.5°	670.9
15°	661.8
17.5°	651.4
20°	639.1
22.5°	626.8
25°	610.3
27.5°	592.7
30°	573.2
32.5°	554.7
35°	533.3
37.5°	510.6
40°	483.9
42.5°	458.3
45°	431.5
47.5°	401.7
50°	368.9
52.5°	334.8
55°	297.8
57.5°	265.1
60°	228.1
62.5°	195.2
65°	162.3
67.5°	131.5
70°	102.7
72.5°	77.0
75°	54.5
77.5°	35.0
80°	20.5
82.5°	12.4
85°	7.1
87.5°	3.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)